

Specification Sheet

Part Number: 157-00360

Off-Set design allows bundles to sit off of mounting points to avoid friction against surrounding areas.

Fir tree gives 3 to 1 extraction versus insertion force making them strong and easy to install.

Friction tab inside of fir tree allows tie to sit in mount without falling out prior to installation.



1-Piece Cable Tie with Fir Tree Mount with Disc, 12.5mm Offset, 8.5"L, 6.1 - 6.9 mm or 6.35 mm (hexagonal)Hole, PA46, Brown, 4000/ctn

Article Number	157-00360
----------------	-----------

Type	T50ROSFT6SO12.5A
------	------------------

Color	Brown (BN)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton's Off-Set Fir Tree Cable Tie and fixing offers a simple and easy to use method of bundling and fixing cables, the design of the fir tree ensures a positive and secure fixing into panels with thicknesses from .2" - .26" or threaded blind holes. The 'disc' on the top of the fir tree covers the hole and minimizes the ingress of water and dirt.
---------------------	--

Short Description	1-Piece Cable Tie with Fir Tree Mount with Disc, 12.5mm Offset, 8.5"L, 6.1 - 6.9 mm or 6.35 mm (hexagonal)Hole, PA46, Brown, 4000/ctn
-------------------	---

Global Part Name	T50ROSFT6SO12.5A-PA46-BN
------------------	--------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	8.5
---------------------	-----

Length L (Metric)	215.9
-------------------	-------

Offset Length (Imperial)	0.49
--------------------------	------

Offset Length (Metric)	12.5
------------------------	------

Fixation Method	Fir tree for round holes
-----------------	--------------------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Width W (Imperial)	0.20
--------------------	------

Width W (Metric)	5.1
------------------	-----

Bundle Diameter Min (Imperial)	0.08
--------------------------------	------

Bundle Diameter Min (Metric)	2.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.97
--------------------------------	------

Bundle Diameter Max (Metric)	50.0
------------------------------	------

Height H (Imperial)	0.87
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.26
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.65
Mounting Hole Diameter D (Imperial)	0.25 " (HEXAGONAL) 0.24 - 0.28 "
Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm 6.35 mm (hexagonal)
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.28
Mounting Hole Diameter D Max (Metric)	6.9
Disc Diameter (Metric)	15.0
Disc Diameter (Imperial)	0.59

Material Polyamide 4.6 (PA46)

Material Shortcut PA46

UV Resistant (Yes/No) No

Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +266°F (-40°C to +130°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	4000
Package Quantity (Metric)	4000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)