


COAXIAL CONNECTOR, MMCX, 50 Ohm, Straight PCB jack (female)

82_MMCX-S50-0-2/111_K

Properties

- Very small size
- Easy to connect and disconnect
- Wide range of board connectors and cable connectors available



Product configuration		
Interface type	Gender	Standard
MMCX	jack	HUBER+SUHNER-MMCX

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	6 GHz

Mechanical data	
Weight	0.0007 kg
Mating cycles	500
Board mounting type	edge mount
Number of printlegs	2
Height above PCB HA	4.45 mm

Engagement / Disengagement force		
	Engagement	Disengagement
Interface force min		6 N
Interface force max	15 N	15 N

COAXIAL CONNECTOR, MMCX, 50 Ohm, Straight PCB jack (female)

82_MMCX-S50-0-2/111_K

Environmental data	
Operation temperature	-55 °C ... 155 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22648789	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
22649679	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
22649680	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22648789	82_MMCX-S50-0-2/111_KE	Single
22649679	82_MMCX-S50-0-2/111_KG	Tape and Reel
22649680	82_MMCX-S50-0-2/111_KH	Bulk 100 pcs

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-PI321 / Date of publication: 12.07.2025 / uncontrolled copy