

Specification Sheet

Part Number: 166-90987



Overlapping conduit design increases mechanical protection and eliminates unintentional exposure of wires caused by motion, vibration or when routed around corners.

Material is easy to use and cut - reduces installation time and labor costs.

Good impact strength; recovers quickly if crushed.

HelaGuard® Non-Metallic Conduit, Double Slit, 1.25" Dia, PP, Black, 82 ft/Std. Reel

Article Number	166-90987
Type	HG-DC1250
Color	Black (BK)
Quantity Per	pack
Product Description	A standard-weight, polypropylene, corrugated two-piece conduit, each of which is slit open to ease installation and maintenance of wire and cable bundles. The interlocking construction is excellent for retrofitting projects. Polypropylene material is typically used in building construction, particulaly where buried in concrete or plaster. Flexible, abrasion resistant and durable for a variety of applications.
Short Description	HelaGuard® Non-Metallic Conduit, Double Slit, 1.25" Dia, PP, Black, 82 ft/Std. Reel

Global Part Name	HG-DC1250-PP-BK
Length L (Imperial)	82.0
Length L (Metric)	25
Inner Diameter D (Imperial)	1.26
Inner Diameter D (Metric)	32
Outside Diameter OD (Imperial)	1.68
Outside Diameter OD (Metric)	42.5
Nominal Diameter (Imperial)	1.25
Nominal Diameter (Metric)	42
Material	Polypropylene (PP)
Material Shortcut	PP
Flammability	EN IEC 61386
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use

Operating Temperature	-4°F to +194°F (-20°C to +90°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	82
Package Quantity (Metric)	25
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)