


Specification Sheet

Part Number: 170-03064

A layer of aluminum provides protection from chemicals, scraping, cuts and abrasion.

Additional layer also provides insulation barrier for vulnerable wires and cables within high temperature environments.

Cuts with ordinary scissors for fast, easy application.



Braided Sleeving, Aluminum Laminated Fiberglass, 1" Dia, AL/GF,Silver, 100 ft/reel

Article Number	170-03064
----------------	-----------

Type	BSHTTST10SR
------	-------------

Color	Silver (SR)
-------	-------------

Quantity Per	pack
--------------	------

Product Description	High Temperature Aluminum Laminated Fiberglass Sleeving is a tubular shaped product that combines the protection of bonded aluminum and fiberglass into a single solution that is able to reflect radiant heat away from the sensitive contents inside the tube.
---------------------	--

Short Description	Braided Sleeving, Aluminum Laminated Fiberglass, 1" Dia, AL/GF,Silver, 100 ft/reel
-------------------	--

Global Part Name	BSHTTST10SR-AL/GF-SR
------------------	----------------------

Length L (Imperial) 100.0

Length L (Metric) 30.48

Bundle Diameter Min (Imperial) 0.1

Bundle Diameter Min (Metric) 2.54

Bundle Diameter Max (Imperial) 0.94

Bundle Diameter Max (Metric) 23.8

Diameter D (Imperial) 1.0

Diameter D (Metric) 25.4

Nominal Diameter (Imperial) 1

Nominal Diameter (Metric) 25.4

Wall Thickness WT (Imperial) 0.025

Wall Thickness WT (Metric) 0.64

Material Aluminum (AL) Glass Fiber (GF)

Material Shortcut AL GF

Halogen Free Yes

UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-76°F to +491°F (-60°C to +255°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	7019905150

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)