

## Specification Sheet


Part Number: 184-22053

Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.

Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.

Mounting holes are uniform in size and are offered every 2 inches to accommodate compact designs and ease installation.

Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.



High-Density Slotted-Wall Wiring Duct, 3" x 3", Non-Adhesive, PVC, Intrinsic Blue, 120 ft/ctn

|                |                      |
|----------------|----------------------|
| Article Number | 184-22053            |
| Type           | SLHD3X3              |
| Color          | Intrinsic Blue (IBU) |
| Quantity Per   | carton               |

|                                  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
|----------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description              | Manufactured from the same PVC material as standard Pro-Duct colors, HellermannTyton also offers an intrinsic blue color option. The intrinsic blue color indicates that the wiring contained in the duct runs to intrinsically safe components in the control panel. HellermannTyton Pro-Duct High-Density, Slotted-Wall Wiring Duct features narrow fingers equaling a 2 to 1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated. |
| Short Description                | High-Density Slotted-Wall Wiring Duct, 3" x 3", Non-Adhesive, PVC, Intrinsic Blue, 120 ft/ctn                                                                                                                                                                                                                                                                                                                                                                                                                                |
| Global Part Name                 | SLHD3X3-PVC-BU                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Length L (Imperial)              | 6.0                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Length L (Metric)                | 1.83                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Width W (Imperial)               | 3.0                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Width W (Metric)                 | 76.2                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Height H (Imperial)              | 3.07                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Height H (Metric)                | 77.9                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Mounting Hole Centers (Imperial) | 2.0                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Material                         | Polyvinylchloride (PVC)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Material Shortcut                | PVC                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |

|                              |                                                  |
|------------------------------|--------------------------------------------------|
| Flammability                 | UL 94 V-0                                        |
| Halogen Free                 | No                                               |
| UV Resistant (Yes/No)        | No                                               |
| Use Conditions               | For Indoor Use Only                              |
| Operating Temperature        | +122°F (+50°C)                                   |
| Reach Compliant (Article 33) | No                                               |
| ROHS Compliant               | Yes                                              |
| Certification/Specification  | UL EN 50085-1:2005 + A1:2013 CSA EN 50085-2-3_1A |
| UL Recognized (US)           | Yes                                              |
| Package Quantity (Imperial)  | 120.0                                            |
| Package Quantity (Metric)    | 36.58                                            |
| Customs Number               | 3925900000                                       |

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)