

75 Ohm, 1 GHz, 85°C, ø2.8 mm, PVC jacket

G_02233-01

Properties

- Custom version of standard RG cable
- 75 Ohm characteristic Impedance



Construction			
Component	Material	Detail	Diameter
Centre conductor	Steel, Copper plated	Wire, 96 %, RAL 9005 - bk	0.24 mm - 0.1 mm
Dielectric	PE (Polyethylene)		1.5 mm
Outer conductor	Copper	Braid, 96%	2 mm
Jacket	PVC (Polyvinyl chloride)	RAL 9005 - bk	2.8 mm +/- 0.1 mm

Electrical data	
Impedance	75 Ω +/- 3Ω
Operating frequency	≤ 1 GHz
Capacitance	67 pF/m
Velocity of signal propagation	66 %
Signal delay	5.03 ns/m
Screening effectiveness	38 dB at frequency 0.01 GHz ... 1GHz
Insulation resistance	100000000 MΩ*m
Operating Voltage (at sea level)	≤ 1 kVrms
Test voltage (50 Hz/1 min)	≤ 2 kVrms
Noise level	10 mV

Mechanical data	
Weight	approx. 13 g/m
Static bending radius	≥ 15 mm
Repeated bending radius	28 mm

Environmental data	
Operation temperature	-25 °C ... 85 °C
Installation temperature	-20 °C ... 60 °C
Fire characteristics	contains halogene

75 Ohm, 1 GHz, 85°C, Ø2.8 mm, PVC jacket

G_02233-01

Suitable connectors	
Cable group	U5

Ordering information		
Item number	Item description	Available as assembly only
22510114	G_02233-01	No

Power Matrix			
Calculation: typical Attenuation [formula: $(a \cdot f^{0.5} + b \cdot f)$] and maximum Power CW [formula: $(p/f^{0.5})$]			
a coefficient typical =	0.8588	b coefficient typical =	0.0352
fmax =	1	P at 1 GHz =	33
Frequency GHz	Nom. attenuation (dB/m)	Nom. attenuation (dB/ft)	CW power (W)
	sea level 25°C ambient temperature	sea level 25°C ambient temperature	sea level 40°C ambient temperature
0.10	0.275	0.084	104
0.20	0.391	0.119	74
0.30	0.481	0.147	60
0.40	0.557	0.170	52
0.60	0.686	0.209	43
0.80	0.796	0.243	37
1.00	0.894	0.272	33

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1083 / Date of publication: 08.08.2024 / uncontrolled copy