

Specification Sheet

Part Number: TSRPFW-RB

Pre-scored knockouts on the base and all four sides remove easily to accomodate all HellermannTyton TSR/TSRP raceway sizes.

Simple two-piece design is easy to install and includes foam tape backing with rubber based adhesive to assist with temporary positioning and mounting.

Accommodates a variety of alarm/detector and fixture makes and models.

PVC construction is lightweight and durable.

Covers are designed to overlap raceway mating points to hide uneven cuts.

Fittings incorporate a minimum 1" bend radius per TIA/EIA 568-B and 569-A standards.

UL 5A Listed to 600V and CSA Certified to 300V (not to exceed 10 lbs. per UL and 5 lbs. per CSA.)



Round Junction Box, 1-1/4" Deep, PVC, Office White, 1/bg

Article Number	250-00210
Type	TSRP-RB
Color	Office White (OEWH)
Quantity Per	pack

Product Description	Designed for mounting of low and line voltage fixtures such as hanging lights, smoke detectors, carbon monoxide detectors and security cameras, the TSRP round junction box complements HellermannTyton's full line of power rated TSRP and low voltage TSR raceway systems. The TSRP round junction box is constructed of a durable PVC material and is available in white, office white and ivory to coordinate with all HellermannTyton surface mount raceway systems.
Short Description	Round Junction Box, 1-1/4" Deep, PVC, Office White, 1/bg
Global Part Name	TSRP-RB-PVC-WH
Length L (Imperial)	5.25
Length L (Metric)	133.35
Width W (Imperial)	5.25
Width W (Metric)	133.35
Height H (Imperial)	1.25
Height H (Metric)	31.75
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Flammability	UL 94 V-0
Halogen Free	No

UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	+122°F (+50°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	3925900000

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com