

MINI250 H-24, SMA (male), SMA (male), 50 Ohm, 26 GHz, 24 in, 609.6 mm

MINI250 H-24

Properties

- Applicable up to 26 GHz
- Part of the "bend-to-the-end" MINIBEND product family
- Direct replacement for 250 size Semi-Rigid cables
- Compliant to MIL-DTL-17 (cable) and MIL-PRF-39012 (connectors)
- Solderless cable junction
- Low loss PTFE dielectric



Product configuration

Type of cable	MINI250 H (32031E)
Type description connector A	29094CR-32-31
Series connector A	SMA, straight - plug
Type description connector B	29094CR-32-31
Series connector B	SMA, straight - plug
Length	609.6 mm
Length	24 inch
Length type	REF to REF

Electrical data

Impedance	50 Ω
Max. operating frequency	26 GHz
VSWR max	1.4
Propagation velocity	77.3 %

Electrical Data (frequency related)

Frequency range	Return loss	VSWR max	Insertion loss
0 GHz ... 2 GHz	21.66 dB	1.18	0.32 dB
2 GHz ... 12 GHz	18.21 dB	1.28	0.81 dB
12 GHz ... 18 GHz	16.53 dB	1.35	1 dB
18 GHz ... 26 GHz	15.56 dB	1.4	1.25 dB

MINI250 H-24, SMA (male), SMA (male), 50 Ohm, 26 GHz, 24 in, 609.6 mm
MINI250 H-24

Mechanical data	
Cable diameter	5.72 mm
Static bending radius	19 mm
Dynamic bending radius	57 mm
Environmental data	
Operation temperature	-55 °C ... 125 °C
Ordering information	
Item number	Item description
85184170	MINI250 H-24

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P44749 / Date of publication: 04.12.2024 / uncontrolled copy