

Specification Sheet

Part Number: 596-73834

White polyester is glossy, allowing for the highest resolution and print contrast.



The acrylic-based adhesive bonds to a wide variety of substrates and can withstand high temperatures long term.

The printable surface is highly resistant to chemicals and solvents and can withstand long-term UV exposure.

Thermal Transfer Labels, High-Bond Adhesive, 3.0" x 1.0", Polyester, White, 3000/roll

Article Number 596-73834

Type PCP3X1

Color White (WH)

Quantity Per pack

Product Description For the ultimate in chemical and solvent resistance and long term outdoor durability, the 840 white polyester offers the most aggressive performance features of any other polyester label material. With an initial outdoor life of 7 years, the labels have been tested far beyond the published limits and the acrylic adhesive bonds well to powder coat painted surfaces as well as baked enamel and slightly textured substrates.

Short Description Thermal Transfer Labels, High-Bond Adhesive, 3.0" x 1.0", Polyester, White, 3000/roll

Global Part Name

PCP3X1-840W-WH

Width W (Imperial)	3.0
Width W (Metric)	76.2
Thickness T (Metric)	64.0
Height H (Imperial)	1.0
Height H (Metric)	25.40
Width of Liner (Metric)	81.28
Width of Liner (Imperial)	3.2
Material	Type 840W, Polyester, white (840W)
Material Shortcut	840W
Adhesive	High Bond Acrylic
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)

Operating Temperature -40°F to +300°F (-40°C to +149°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Certification/Specification CSA 66956

UL Recognized (US) Yes

Package Quantity (Imperial) 3000

Package Quantity (Metric) 3000

Customs Number 3919102055

Labels per Column 1

Labels per Row 1

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)