



Metallic conduits with plastic coating

• LFHCS Galvanised Steel Conduit, LFH Coating

Rail industry, underground stations, tunnels, public buildings, wherever high fire protection is required.

Features and Benefits

- Self-extinguishing to UL94 V0
- Low smoke, low toxicity
- High compression, tensile and impact strength
- Very flexible
- Halogen, sulphur and phosphorus free




HeliaGuard LFHCS galvanised steel conduit is low smoke, low toxicity, highly flame retardant and halogen free.

MATERIAL	Galvanised Steel (GS), Polyolefin (PO)
Operating Temperature	-25 °C to +90 °C
Flammability	UL94 V0
Specifications	Lloyd's Register

HF ✓

RoHS ✓



HeliaGuard metallic conduit, plastic coating

TYPE	Nominal Ø	Outside Ø (OD)	Inside Ø (ID)	Min. Bending Radius (R)	Weight (g/m)	Reel Length	Colour	Article-No.
LFHCS12	12	14.2	10.0	30	199	25 m	Black (BK)	166-30900
LFHCS16	16	17.1	12.9	40	216	25 m	Black (BK)	166-30901
LFHCS20	20	21.6	16.8	45	350	25 m	Black (BK)	166-30902
LFHCS25	25	26.0	20.9	55	420	25 m	Black (BK)	166-30903
LFHCS32	32	34.0	27.8	60	571	25 m	Black (BK)	166-30904
LFHCS40	40	44.2	37.3	80	739	10 m	Black (BK)	166-30905
LFHCS50	50	55.0	48.0	90	1,077	10 m	Black (BK)	166-30906
LFHCS63	63	64.5	57.0	115	1,126	10 m	Black (BK)	166-30907
LFHCS75	75	79.2	69.4	150	1,509	10 m	Black (BK)	166-30908

All dimensions in mm. Subject to technical changes.

Other reel lengths available on request. Minimum Order Quantity (MOQ) may differ from package content.