



Heat Shrinkable Tubing adhesive lined

EPS-300 - 3:1 shrink ratio

EPS-400 - 4:1 shrink ratio

Heat shrinkable tubing EPS seals and protects a wide variety of electrical applications like back end connector sealing, connector-to-cable transitions and splices.

Features and Benefits

- Flexible, thin walled polyolefin heat shrink tubing
- With coextruded hot melt adhesive inner wall
- Protects against moisture
- Provides an environmental sealing of complex parts



PTA300 and PTA400 offer high shrink ratios and protection against humidity.



**Cut lengths available on request.
Please contact us!**



Heat Shrinkable Tubing 3:1 with adhesive



Heat Shrinkable Tubing 4:1 with adhesive

MATERIAL	Polyolefin, cross-linked (PO-X)
Operating Temperature	-55 °C to +125 °C
Minimum Shrink Temperature	+120 °C
Longitudinal change after shrinkage	-10 % max.
Softening Point Adhesive	+90 °C
Dielectric Strength	15 kV/mm according to IEC 60684 P2
Flammability	ASTM D2671 (outer layer only)
Specifications	SAE - AMS - DTL-23053 / 4

RoHS ✓

TYPE	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Reel Length	Colour	Shrink Ratio	Article-No.
EPS-300-3/1	3.0	1.0	1.00	400 m	Black (BK)	3:1	340-03010
EPS-300-6/2	6.0	2.0	1.00	300 m	Black (BK)	3:1	340-06020
EPS-300-9/3	9.0	3.0	1.40	150 m	Black (BK)	3:1	340-09030
EPS-300-12/4	12.0	4.0	1.80	100 m	Black (BK)	3:1	340-12040
EPS-300-19/6	19.0	6.0	2.20	50 m	Black (BK)	3:1	340-19060
EPS-300-24/8	24.0	8.0	2.50	25 m	Black (BK)	3:1	340-24080
EPS-300-40/13	40.0	13.0	2.50	25 m	Black (BK)	3:1	340-40130

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.

TYPE	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Reel Length	Colour	Shrink Ratio	Article-No.
EPS-400-4/1	4.0	1.0	1.00	300 m	Black (BK)	4:1	341-04010
EPS-400-8/2	8.0	2.0	1.00	150 m	Black (BK)	4:1	341-08020
EPS-400-12/3	12.0	3.0	1.40	100 m	Black (BK)	4:1	341-12030
EPS-400-16/4	16.0	4.0	1.80	100 m	Black (BK)	4:1	341-16040
EPS-400-24/6	24.0	6.0	2.20	50 m	Black (BK)	4:1	341-24060
EPS-400-32/8	32.0	8.0	2.50	25 m	Black (BK)	4:1	341-32080

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.



For product specific approvals and specifications please refer to the Appendix.