



### Light weight standard polyester braided sleeving

#### Helagaine HEGPL

Helagaine HEGPL is used primarily in automobile interiors, motor compartments, car bodies and underfloors.

#### Features and Benefits

- Made of sturdy polyester
- Expansion rate of 3:1
- Easier application over irregular shapes
- Highly flexible
- Good abrasion resistance



Helagaine HEGPL braided sleeving.

|                              |                                         |
|------------------------------|-----------------------------------------|
| <b>MATERIAL</b>              | Polyester (PET)                         |
| <b>Operating Temperature</b> | -50 °C to +150 °C, intermittent +220 °C |
| <b>Melting Point</b>         | +250 °C                                 |
| <b>Flammability</b>          | UL94 V2, FMVSS 302, Type B              |

**RoHS** ✓



To prevent fraying, the sleeve can be cut with the hot cutting tool HSG0. See page 533.

| TYPE    | Bundle<br>Ø min. | Bundle<br>Ø max. | Colour     | Reel<br>Length | Article-No. |
|---------|------------------|------------------|------------|----------------|-------------|
| HEGPL03 | 3.0              | 8.0              | Black (BK) | 1,000 m        | 170-80503   |
| HEGPL06 | 5.0              | 12.0             | Black (BK) | 400 m          | 170-80506   |
| HEGPL12 | 8.0              | 21.0             | Black (BK) | 300 m          | 170-80512   |
| HEGPL20 | 12.0             | 30.0             | Black (BK) | 300 m          | 170-80520   |
| HEGPL30 | 18.0             | 55.0             | Black (BK) | 200 m          | 170-80530   |
| HEGPL40 | 24.0             | 66.0             | Black (BK) | 150 m          | 170-80540   |
| HEGPL50 | 30.0             | 82.0             | Black (BK) | 150 m          | 170-80550   |

All dimensions in mm. Subject to technical changes.

Colour grey available on request. Cuts in any lengths. Minimum Order Quantity (MOQ) may differ from package content.