



# **SPECIFICATION FOR APPROVAL**

Customer : STD

## Description : DC FAN

Customer Part No. REV. :

Delta Model No. : FFB0424EHN-CP0 REV. : 00

Sample Issue No. :

Sample Issue Date : APR.01.2024

PLEASE SEND ONE COPY OF THIS SPECIFICAITON BACK AFTER  
YOU SIGNED APPROVAL FOR PRODUCTION PRE-ARRANGMENT.

**APPROVED BY:**

DATE :

DELTA ELECTRONICS, INC.

## DEPARTMENT TAOYUAN PLANT

252, SHANGYING ROAD, GUISHAN INDUSTRIAL ZONE,  
TAOYUAN CITY 33341, TAIWAN

TEL:886-(0)3-3591968

FAX:886-(0)3-3591991

## \*\*\* SAMPLE HISTORY\*\*\*

CUSTOMER: STD

**CUSTOMER P/N:**

DELTA MODEL: FFB0424EHN-CP0

DELTA ELECTRONICS, INC.  
252, SHANGYING ROAD, GUISHAN INDUSTRIAL ZONE,  
TAOYUAN CITY 33341, TAIWAN

TEL : 886-(0)3-3591968  
FAX : 886-(0)3-3591991

## **STATEMENT OF DEVIATION**

NONE

DESCRIPTION:

DELTA ELECTRONICS, INC.

252, SHANGYING ROAD, GUISHAN INDUSTRIAL ZONE,  
TAOYUAN CITY 33341, TAIWAN

TEL : 886-(0)3-3591968  
FAX : 886-(0)3-3591991

## SPECIFICATION FOR APPROVAL

Customer : STD

Description : DC FAN

Customer P/N : \_\_\_\_\_ rev. :

Delta model no. : FFB0424EHN-CP0 Delta Safety Model No.: FFB0424EHN-C

Sample revision. : 00 Issue no.:

Sample issue date : APR.01.2024 Quantity :

### 1. SCOPE:

THIS SPECIFICATION DEFINES THE ELECTRICAL AND MECHANICAL CHARACTERISTICS OF THE DC BRUSHLESS AXIAL FLOW FAN.

### 2. CHARACTERS:

ITEM	DESCRIPTION
RATED VOLTAGE	24.0 VDC
OPERATION VOLTAGE RANGE	20.4 - 26.4 VDC
INPUT CURRENT(AVG.)★ (AT RATED VOLTAGE / FREE AIR)	0.15 (MAX. 0.20) A SAFETY CURRENT ON LABEL : 0.28A
INPUT POWER(AVG.)★ (AT RATED VOLTAGE / FREE AIR)	3.60 (MAX. 4.80) W
SPEED (AT RATED VOLTAGE / FREE AIR)	13100 ± 10% R.P.M.
MAX. AIR FLOW (AT ZERO STATIC PRESSURE)	0.50 (MIN. 0.45) M <sup>3</sup> /MIN. 17.67 (MIN. 15.903) CFM
MAX. AIR PRESSURE (AT ZERO AIRFLOW)	26.41 (MIN. 21.39) mmH <sub>2</sub> O 1.04 (MIN. 0.842) inchH <sub>2</sub> O
ACOUSTICAL NOISE (AVG.)	50.0 (MAX. 54.0) dB-A
INSULATION TYPE	UL: CLASS A
INSULATION STRENGTH	10 MEG OHM MIN. AT 500 VDC (BETWEEN FRAME AND (+) TERMINAL)
DIELECTRIC STRENGTH	5 mA MAX. AT 500 VAC 50/60 Hz ONE MINUTE, (BETWEEN FRAME AND (+) TERMINAL)

★AVG. IS THE AVERAGE VALUE DURING STEADY OPERATION, AND MAX. IS MAXIMUM AVERAGE VALUE INCLUDED PRODUCTION TOLERANCE. ABOUT THE PEAK VALUE, NEED TO USE OSCILLOSCOPE TO MEASURE.

(continued)

---

PART NO:

---


DELTA MODEL: FFB0424EHN-CP0

---

LIFE EXPECTANCE (L10) (AT LABEL VOLTAGE)	70,000 HOURS CONTINUOUS OPERATION AT 40 °C WITH 15 ~ 65 %RH.
ROTATION	CLOCKWISE VIEW FROM NAME PLATE SIDE.
LOCKED ROTOR PROTECTION	THE CURRENT WILL SHUT DOWN, WHEN ROTOR LOCKED AND FIXED.

NOTES:

1. ALL READINGS ARE MEASURED AFTER STABLY WARMING UP THROUGH 10 MINUTES.
2. STANDARD AIR PROPERTY IS AIR AT (Td) 25°C TEMPERATURE, (RH) 65% RELATIVE HUMIDITY, AND (Pb) 760 mmHg BAROMETRIC PRESSURE.
3. THE VALUES WRITTEN IN PARENS, ( ), ARE LIMITED SPEC.
4. ACOUSTICAL NOISE MEASURING CONDITION:



NOISE IS MEASURED AT RATED VOLTAGE IN FREE AIR IN SEMI-ANECHOIC CHAMBER WITH MICROPHONE AT A DISTANCE OF ONE METER FROM THE FAN INTAKE.

---

PART NO:

---

DELTA MODEL: FFB0424EHN-CP0

---

3. MECHANICAL:

3-1. DIMENSIONS-----	SEE DIMENSIONS DRAWING
3-2. FRAME-----	PLASTIC UL: 94V-0
3-3. IMPELLER-----	PLASTIC UL: 94V-0
3-4. BEARING SYSTEM-----	TWO BALL BEARINGS
3-5. WEIGHT-----	47 GRAMS(REF.)

4. ENVIRONMENTAL:

4-1. OPERATING TEMPERATURE-----	-10 TO +70 DEGREE C
4-2. STORAGE TEMPERATURE-----	-40 TO +75 DEGREE C
4-3. OPERATING HUMIDITY-----	5 TO 90 % RH
4-4. STORAGE HUMIDITY-----	5 TO 95 % RH

5. PROTECTION:

5-1. LOCKED ROTOR PROTECTION

IMPEDANCE OF MOTOR WINDING PROTECTS MOTOR FROM FIRE IN  
96 HOURS OF LOCKED ROTOR CONDITION AT THE RATED VOLTAGE.

5-2. POLARITY PROTECTION

BE CAPABLE OF WITHSTANDING IF REVERSE CONNECTION FOR  
POSITIVE AND NEGATIVE LEADS.

6. RE OZONE DEPLETING SUBSTANCES:

6-1. NO CONTAINING PBBs, PBBOs, CFCs, PBBEs, PBDPEs AND HCFCs.

7. PRODUCTION LOCATION

7-1. PRODUCTS WILL BE PRODUCED IN CHINA OR THAILAND.

8. FAN MAY HAVE MULTIPLE SOURCES FOR RAW MATERIALS.

MAIN MATERIALS AND ALTERNATIVE MATERIALS WILL MEET FAN  
SPEC CHARACTERISTIC.

---


PART NO:

---

DELTA MODEL: FFB0424EHN-CP0

---

9. P & Q CURVE:



\*TEST CONDITION: INPUT VOLTAGE-----OPERATION VOLTAGE  
TEMPERATURE-----ROOM TEMPERATURE  
HUMIDITY-----65%RH

PART NO:

DELTA MODEL: FFB0424EHN-CP0

#### 10. DIMENSION DRAWING:

##### LABEL CONTENT:






OR



OR



OR



AIR DIRECTION

UNIT:mm(INCH)

##### NOTES:

1. CABLE WIRE: UL10368 AWG#28
  - RED WIRE ----- (+)
  - BLUE WIRE ----- (F00)
  - YELLOW WIRE ----- (PWM)
  - BLACK WIRE ----- (-)
2. THIS PRODUCT IS RoHS COMPLIANT
- ★ 3. IF THE CUSTOMER NEEDS TO CRIMP THE TERMINAL BY HIMSELF, PLEASE ENSURE THAT THE MACHINE IS WELL GROUNDED BEFORE CRIMPING THE TERMINAL TO AVOID ACCIDENTAL ABNORMAL VOLTAGE AFFECTING THE FAN.

---

PART NO:


---

DELTA MODEL: FFB0424EHN-CP0

---

11. FREQUENCY GENERATOR (FG) SIGNAL:

11-1. OUTPUT CIRCUIT - OPEN COLLECTOR MODE:




CAUTION:

THE LEAD WIRE OF FG SIGNAL CAN NOT TOUCH THE LEAD WIRE OF POSITIVE OR NEGATIVE.

11-2. SPECIFICATION:

$V_{FG}$  = 5.0 TYP. ( $V_{cc}$  MAX.)    $I_c$  = 5mA MAX.  
 $V_{CE}$  = 0.8V MAX.    $R \geq V_{FG} / I_c$

11-3. FREQUENCY GENERATOR WAVEFORM:



---

PART NO:


---

DELTA MODEL: FFB0424EHN-CP0

---

## 12. PWM CONTROL SIGNAL:

12-1 SIGNAL VOLTAGE RANGE: 0~5.0VDC



- THE PREFERRED OPERATING POINT FOR THE FAN IS 25KHZ.
- AT 100% DUTY CYCLE, THE ROTOR WILL SPIN AT MAXIMUM SPEED.
- AT 0% DUTY CYCLE, THE ROTOR WILL STOP.
- WITH CONTROL SIGNAL LEAD DISCONNECTED, THE FAN WILL SPIN AT MAXIMUM SPEED.

## 12-2 THE REQUIREMENT OF WAVEFORM QUALITY OF PWM SIGNAL

- THE RECOMMENDED PWM SIGNAL FROM SYSTEM IS TTL ( $t_r = 500\text{ns}$ ,  $t_f = 500\text{ns}$ ), EVEN IF THE PWM LEAD OF FAN IS DISCONNECTED.
- THE MAXIMUM PERMISSIBLE OF WAVEFORM DISTORTION:

$$V_{IH} : (V_+ - 0.5) * 90\% \quad \text{RISE TIME : } t_r < 500\text{ns}$$

$$V_{IL} : (V_+ - 0.5) * 10\% \quad \text{FALL TIME : } t_f < 500\text{ns}$$



## 12-3 SPEED VS PWM CONTROL SIGNAL:

(AT 25°C, RATED VOLTAGE & PWM SIGNAL AS FOLLOW)

\*PWM SIGNAL

PWM FREQUENCY = 25KHz

DUTY CYCLE (%)	SPEED (R.P.M.)	CURRENT(A) (AVG.)★
100	13100±10%	0.15 (MAX. 0.20)
0	0	0.02 (MAX. 0.03)



★AVG. IS THE AVERAGE VALUE DURING STEADY OPERATION, AND MAX. IS MAXIMUM AVERAGE VALUE INCLUDED PRODUCTION TOLERANCE. ABOUT THE PEAK VALUE, NEED TO USE OSCILLOSCOPE TO MEASURE.

- MIN. STARTED DUTY CYCLE(at 25°C, 24.0VDC): 30 %  
WHEN THE FAN BLADE IS IN THE COMPLETE STOP STATE AND THEN PROVIDE PWM TO START THE FAN IN ORDER TO ENSURE THAT THE FAN START-UP IS NORMAL FROM A DEAD STOP.

---

PART NO:

---

DELTA MODEL: FFB0424EHN-CP0

---

### 13. FAN CABLE ADDITIONAL PROCESS OUTSIDE DELTA

#### 13-1. HANDLING :

13-1-1. DO NOT PRESS ROTOR OR PULL CABLE IN ANY PROCESS.



13-1-2. WEARING ELECTROSTATIC GLOVES BEFORE WORKING, MAKE SURE HOUSING ASSAMBLING MECHINE, WORKING TABLE WITH ELECTROSTATIC PROTECTION.

13-1-3. DO NOT WEAR OR DROP THE FAN DURING ALL PROCESS, PLEASE SCRAPE DROOPPED FAN TO AVOID BEARING DAMAGE.


#### 13-2. TESTING :

13-2-1. MAKE SURE FAN SPEED AND FUNCTION WORKS WELL AFTER ASSAMBLY.



#### 13-3. PACKING:

13-3-1. BE SURE OF FAN DIRECTION AND HOUSING POSITION, CAN'T INTERFER CARTON OR POTTION OR OTHER MATERIAL.




13-3-2. MAKE SURE DESICCANT, QUANTITY AND P/N IS CORRECT BEFORE PACKING.



PART NO:

DELTA MODEL: FFB0424EHN-CP0


14. SCREW SPECIFICATION:




SELF-TAPPING SCREW  
FLANGE MOUNTING DRAWING



FLANGE TYPE



MECHANICAL SCREW  
FLANGE MOUNTING DRAWING




SELF-TAPPING SCREW  
RIB MOUNTING DRAWING




RIB TYPE(ALL RIB)

RIB TYPE(HALF FLANGE & HALF RIB)



MECHANICAL SCREW  
RIB MOUNTING DRAWING



MECHANICAL SCREW  
FLANGE MOUNTING DRAWING

NOTE:

- 1.SELF-TAPPING SCREW ACCORDING TO JIS B 1122 TYPE 2
- 2.EACH SCREW HOLE CAN ONLY TIGHTENED ONCE WHEN USING SELF-TAPPING SCREW
- 3.IF IT WAS SLIPPAGE OR BREAK WHEN TIGHTENED SELF-TAPPING SCREW,  
THEN CAN USING LOWER TORQUE THAN WE RECOMMENDED IN TABLE A .

\* FOLLOW JIS B 1007

TABLE A: MOUNTING HOLE WITH RECOMMENDED SCREW

FAN TYPE		MOUNTING HOLE DIAMETER	SCREW TYPE	SCREW SPEC.	SCREW OUTER DIMENSION. (mm)		RECOMMENDED MAX. TORQUE (kgf-cm)	
					MAXIMUM	MINIMUM	FLANGE TYPE	RIB TYPE
<input type="checkbox"/>	FLANGE	$\Phi 3.2$	SELF-TAPPING	ST3.5*1.3	3.53	3.35	4.5	5.5
<input type="checkbox"/>	RIB		MECHANICAL	M3.0x0.5	2.98	2.88	4.5	7.5
<input type="checkbox"/>	FLANGE		SELF-TAPPING	ST4.0x1.41	4	3.85	5.5	
<input checked="" type="checkbox"/>	RIB		MECHANICAL	M3.0x0.5	2.98	2.88	4.5	
<input type="checkbox"/>	FLANGE	$\Phi 4.3$	SELF-TAPPING	*ST4.8x1.6	4.8	4.62	5.5	7.5
<input type="checkbox"/>	RIB		MECHANICAL	M4x0.7	3.97	3.84	4.5	
<input type="checkbox"/>	FLANGE		SELF-TAPPING	*ST5.0x1.59	5	4.85	5.5	
<input type="checkbox"/>	RIB		SELF-TAPPING	*ST4.8x1.6	4.8	4.62	5.5	
<input type="checkbox"/>	RIB		MECHANICAL	M4x0.7	3.97	3.84	4.5	



## Application Notice

1. Delta will not guarantee the performance of the products if the application condition falls outside the parameters set forth in the specification.
2. A written request should be submitted to Delta prior to approval if deviation from this specification is required.
3. Please exercise caution when handling fans. Damage may be caused when pressure is applied to the impeller, if the fans are handled by the lead wires, or if the fan was hard-dropped to the production floor.
4. Except as pertains to some special designs, there is no guarantee that the products will be free from any such safety problems or failures as caused by the introduction of powder, droplets of water or encroachment of insect into the hub.
5. The above-mentioned conditions are representative of some unique examples and viewed as the first point of reference prior to all other information.
6. It is very important to establish the correct polarity before connecting the fan to the power source. Positive (+) and Negative (-). Damage may be caused to the fans if connection is with reverse polarity, if there is no foolproof method to protect against such error specifically mentioned in this spec.
7. Delta fans without special protection are not suitable where any corrosive fluids are introduced to their environment.
8. Please ensure all fans are stored according to the storage temperature limits specified. Do not store fans in a high humidity environment. We highly recommend performance testing is conducted before shipping, if the fans have been stored over 6 months.
9. Not all fans are provided with the Lock Rotor Protection feature. If you impair the rotation of the impeller for the fans that do not have this function, the performance of those fans will lead to failure.
10. Please be cautious when mounting the fan. Incorrect mounting of fans may cause excess resonance, vibration and subsequent noise.
11. It is important to consider safety when testing the fans. A suitable fan guard should be fitted to the fan to guard against any potential for personal injury.
12. Except where specifically stated, all tests are carried out at room (ambient) temperature and relative humidity conditions of 25°C, 65% RH. The test value is only for fan performance itself.
13. Be certain to connect an “4.7µF or greater” capacitor to the fan externally when the application calls for using multiple fans in parallel, to avoid any unstable power.
14. Be sure that the machine is well grounded before doing crimping terminal of cable wire in order to avoid any impact due to an unexpected abnormal voltage to the fan .