

MICROWAVE TEST ASSEMBLIES, 1.85mm (male), 1.85mm (male), 50 Ohm, 70 GHz, 24in

SF570E/11PC185/11PC185/24in

Properties

- Applicable up to 70 GHz
- High phase- and amplitude stability with flexure and movement
- Excellent insertion and return loss
- Precise and repeatable measurements
- Long life time - lower measurement cost
- Return loss figures are guaranteed up to 67 GHz



Product configuration

Type of cable	SUCOFLEX_570_E
Type description connector A	SF_11_PC185-503
Series connector A	PC 1.85, straight - plug
Type description connector B	SF_11_PC185-503
Series connector B	PC 1.85, straight - plug
Length	610 mm
Length	24 inch
Length type	REF to REF

Electrical data

Impedance	50 Ω
Max. operating frequency	70 GHz
Min. return loss	14 dB
VSWR max	1.499
Max. insertion loss	4.63 dB
Signal delay	4.3 ns/m
Propagation velocity	77 %
Min. screening effectiveness	90 dB
Max. screening frequency	18 GHz
Amplitude stability vs. flexure	+/- 0.1 dB
Phase stability vs. flexure	+/- 10 °

MICROWAVE TEST ASSEMBLIES, 1.85mm (male), 1.85mm (male), 50 Ohm, 70 GHz, 24in SF570E/11PC185/11PC185/24in

Mechanical data			
Cable diameter		3.3 mm	
Static bending radius		11 mm	
Environmental data			
Operation temperature		-40 °C ... 85 °C	
Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
85184843	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
Comment			
SUCOFLEX 570E microwave cable assemblies set a new measurement standard through 70 GHz			
Return loss figures are guaranteed up to 67 GHz.			
Ordering information			
Item number	Item description		
85184843	SF570E/11PC185/11PC185/24in		

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P37453 / Date of publication: 10.04.2025 / uncontrolled copy