

MICROWAVE TEST ASSEMBLIES, N (male), N (male), 50 Ohm, 18 GHz, 1500mm

ST18A/11N/11N/1500mm

Properties

- Applicable up to 18 GHz
- High flexibility in spite of armouring
- Phase and loss stability with flexure
- Crush-, torque- and kink-resistant
- Waterproof IP68



Product configuration	
Type of cable	SUCOTEST_18A
Type description connector A	SF_11_N-468
Series connector A	N, straight - plug
Type description connector B	SF_11_N-468
Series connector B	N, straight - plug
Armour	A-Armour SUCOTEST 18A, 85°C, ø10.2 mm, PUR jacket
Length	1500 mm
Length type	REF to REF
Electrical data	
Impedance	50 Ω
Max. operating frequency	18 GHz
Min. return loss	19 dB
VSWR max	1.253
Max. insertion loss	2.03 dB
Signal delay	4.3 ns/m
Propagation velocity	77 %
Mechanical data	
Weight	0.3 kg
Cable diameter	10.3 mm
Static bending radius	30 mm
Environmental data	
Operation temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	Mated / IP68

MICROWAVE TEST ASSEMBLIES, N (male), N (male), 50 Ohm, 18 GHz, 1500mm

ST18A/11N/11N/1500mm

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84013029	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c

Comment

Sucotest 18A armoured test assemblies offer excellent electrical performance (low insertion loss combined with unique stability and excellent return loss) for heavy duty, outdoor and harsh environment measurements up to 18 GHz.

Ordering information

Item number	Item description
84013029	ST18A/11N468/11N468/1500mm

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P10488 / Date of publication: 09.04.2025 / uncontrolled copy