

LOCTITE ABLESTIK 2033SC

April 2014

PRODUCT DESCRIPTION

LOCTITE ABLESTIK 2033SC provides the following product characteristics:

Technology	Proprietary Hybrid Chemistry
Appearance	red
Cure	Heat cure
Product Benefits	• Non-conductive • Single component • Low bleed • Long work life • Low cure temperature • Fast cure • Optimized rheology
Application	Die attach
pH	3.6
Filler Type	Silica

LOCTITE ABLESTIK 2033SC die attach adhesive is designed for high throughput smart card bonding applications. It is compatible with various encapsulant chemistries.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Thixotropic Index (0.5/5 rpm)	6.1
Viscosity, Brookfield CP51, 25 °C, mPa·s (cP):	
Speed 5 rpm	11,300
Work Life @ 25°C, hours	24
Shelf Life @ -40°C (from date of manufacture), days	365

TYPICAL CURING PERFORMANCE

Cure Schedule

90 seconds @ 110°C

Alternative Cure Schedule 1

60 seconds @ 120°C

Alternative Cure Schedule 2

10 seconds @ 150°C

Weight Loss on Cure

10 x 10 mm Si die on glass slide, %	0.5
-------------------------------------	-----

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Coefficient of Thermal Expansion :	
Below Tg, ppm/°C	56
Above Tg, ppm/°C	133
Glass Transition Temperature (Tg) by TMA, °C	46
Tensile Modulus, DMTA :	
@ -65 °C	N/mm ² 4,200 (psi) (600,000)
@ 25 °C	N/mm ² 2,100 (psi) (300,000)
@ 150 °C	N/mm ² 30 (psi) (4,200)
@ 200 °C	N/mm ² 60 (psi) (8,600)
Extractable Ionic Content, ppm:	
Chloride (Cl-)	<30
Sodium (Na+)	<15
Potassium (K+)	<5
Water Extract Conductivity, µmhos/cm	130

TYPICAL PERFORMANCE OF CURED MATERIAL

Miscellaneous

Die Shear Strength vs Temperature, kg-f:

3 X 3 mm, Si die, MPa (psi)

Substrate	
PBGA-FR4	20 (3,000)

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

THAWING:

1. Allow container to reach room temperature before use.
2. After removing from the freezer, set the syringes to stand vertically while thawing.
3. DO NOT open the container before contents reach 25°C temperature. Any moisture that collects on the thawed container should be removed prior to opening the container.
4. DO NOT re-freeze. Once thawed to -40°C, the adhesive should not be re-frozen.

DIRECTIONS FOR USE

1. Thawed material should immediately be placed on dispense equipment for use.
2. If the adhesive is transferred to a final dispensing reservoir, care must be exercised to avoid entrapment of contaminants and/or air into the adhesive.
3. Adhesive must be completely used within the product's recommended work life.

Not for product specifications

The technical data contained herein are intended as reference only.

Please contact your local quality department for assistance and recommendations on specifications for this product.

STORAGE:

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: -40 °C. Storage below minus (-)40 °C or greater than minus (-)40 °C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{psi} \times 145 = \text{N/mm}^2$
 $\text{MPa} = \text{N/mm}^2$
 $\text{N} \cdot \text{m} \times 8.851 = \text{lb} \cdot \text{in}$
 $\text{N} \cdot \text{m} \times 0.738 = \text{lb} \cdot \text{ft}$
 $\text{N} \cdot \text{mm} \times 0.142 = \text{oz} \cdot \text{in}$
 $\text{mPa} \cdot \text{s} = \text{cP}$

Disclaimer

Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage: [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Reference 2