

LOCTITE ABLESTIK 2111 BIPAX

December 2016

PRODUCT DESCRIPTION

LOCTITE ABLESTIK 2111 BIPAX provides the following product characteristics:

Technology	Epoxy
Color	Hazy white
Cure	Room temperature cure or Heat cure
Operating Temperature	-70 to 100 °C
Product Benefits	<ul style="list-style-type: none"> Long pot life Good wetting Non-sag Non-drip rheology Improved impact strength Excellent thermal and mechanical shock resistance Excellent environmental resistance
Mix Ratio, by weight - Resin : Hardener	100 : 30
Application	Assembly
Typical Assembly Applications	Bonding, Laminating, Staking, Repair and Manufacturing
Substrates	Glass, Ceramic, Fabric, Wood, Leather, Glass fabrics, Most metals and Many plastics

LOCTITE ABLESTIK 2111 BIPAX is a thixotropic epoxy resin and hardener formulated for ease of use. This two part adhesive system contains no volatile solvents.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Mixed Viscosity @ 25 °C, mPa·s (cP):

Spindle TF, Speed 10 rpm	40,000
Specific Gravity, mixed	1.24

Pot Life:

@ 25 grams, minutes	40
@ 100 grams, minutes	20

TYPICAL CURING PERFORMANCE

Cure Schedule

24 hours @ 25°C

Alternative Cure Schedule

4 hours @ 25°C plus 4 hours @ 65°C plus

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Coefficient of Expansion, cm/cm/°C	5.5×10 ⁻⁵
Glass Transition Temperature (T _g), °C, ultimate	45.0
Hardness, Shore D	82
Refractive Index	1.53
Water Absorption, after 24 hours, %	3.3
Izod Impact Strength, ft-lb/in. of notch	2
Elongation, %	26

Outgassing Properties

VOC, grams/liter	31.2
------------------	------

Electrical Properties

Volume Resistivity, ohm-cm @ 25°C	9.50×10 ⁰⁸
-----------------------------------	-----------------------

TYPICAL PERFORMANCE OF CURED MATERIAL

Lap Shear Strength :

Aluminum to Aluminum	N/mm ²	24
	(psi)	(3,500)

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

DIRECTIONS FOR USE

- Carefully clean and dry all surfaces to be bonded
- Remove clamp and thoroughly mix the LOCTITE ABLESTIK 2111 BIPAX epoxy adhesive system components in the handy BIPAX mixing-dispenser package until color is uniform throughout
- Apply this completely mixed adhesive to the prepared surfaces, and gently press these surfaces together. Contact pressure is adequate for strong, reliable bonds; however, maintain contact until adhesive is completely cured
- Some ingredients in this formulation provided in BIPAX, TRA-PAX and bulk packaging may crystallize when subjected to low temperature storage. A gentle warming cycle of 52°C for 30 minutes prior to mixing components may be necessary. Crystallized epoxy components do not react as well as liquid components and should be redissolved prior to use for best results

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

STORAGE:

The expiration date is based upon dry storage conditions at or below 27°C, unless specified otherwise on the packaging, in the original, sealed and unopened containers for BIPAX, TRA-PAX and bulk packaged materials. The expiration date for pre-mixed and frozen materials is based upon dry storage conditions at or below the temperature indicated on each package. Contents may separate during storage. Resin or hardener in bulk containers (e.g., quarts, gallons) should be thoroughly mixed prior to combining them to obtain all the benefits of the properties designed into the formulation.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{psi} \times 145 = \text{N/mm}^2$
 $\text{MPa} = \text{N/mm}^2$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Disclaimer**Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically**

disclaims any liability for consequential or incidental damages of any kind, including lost profits. The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage: [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Reference 1

Americas
+1.888.943.6535

Europe
+32.1457.5611

Asia
+86.21.3898.4800

For the most direct access to local sales and technical support visit: www.henkel.com/electronics