

868 / 915 MHz Weather-Proof Whip Antenna



AANE-WH-0039

Request Samples



Check Inventory



Ø13 x 195 mm

RoHS/RoHS II Compliant

MSL Level = N/A

Features

- 868 / 915 MHz Antenna
- High Peak Gain 1.7dBi
- High Efficiency up to 85%
- Swivel Connector Design for Straight, Right-Angle and 45-degree Positioning
- Weather-Proof and IP65 Rated
- Fully Customizable Connectors

Applications

- LPWA/LoRa/SigFox Applications
- Intelligent Lighting
- Smart Metering Solutions
- Smart Irrigation Systems
- Home Automation and Fire Prevention
- Agriculture/Environment Sensing

Product Image



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

868 / 915 MHz Weather-Proof Whip Antenna



AANE-WH-0039

Request Samples



Check Inventory



Ø13 x 195 mm

RoHS/RoHS II Compliant

MSL Level = N/A

Electrical Specification

Parameter	Specification		Unit
Operating Frequency	Europe (863-870 MHz)	US (902-928 MHz)	MHz
VSWR(Typ.)	2.0		
Peak Gain	1.3	1.8	dBi
Maximum Efficiency	85.6	83.8	%
Average Efficiency	81	77	%
Impedance	50		Ω
Polarization	Linear		
Radiation Pattern (Azimuth)	Omni-directional		
Max Power - Ambient 25°C	5		W

Mechanical Specification

Parameter	Specification
Dimensions	Ø13 x 195 mm
Material	UV Resistant ABS (Optional)
Recommended Torque for Mounting	0.565 N·m
Color	Black
Antenna Type	Whip (Dipole)
RF Connector ⁽¹⁾	SMA(M)

(1): Fully Customizable RF Connectors

Environmental Specification

Parameter	Specification
Operating Temperature	-40°C to +85°C
Storage Temperature	-40°C to +85°C
IP Rating	IP65 (Optional)
RoHS Complaint	Yes



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

868 / 915 MHz Weather-Proof Whip Antenna



AANE-WH-0039

Request Samples



Check Inventory



Ø13 x 195 mm

RoHS/RoHS II Compliant

MSL Level = N/A

Ordering Information

Part Number	Description	Connector Option
AANE-WH-0039-1	868 / 915 MHz Weather-Proof Whip Antenna with SMA(M) Connector, IP65 & UV-Resistant Housing	SMA(M)
AANE-WH-0039-2	868 / 915 MHz Weather-Proof Whip Antenna with RP-SMA(M) Connector, IP65 & UV-Resistant Housing	RP-SMA(M)
AANE-WH-0039-3	868 / 915 MHz Whip Antenna with SMA(M) Connector	SMA(M)
AANE-WH-0039-4	868 / 915 MHz Whip Antenna with RP-SMA(M) Connector	RP-SMA(M)

Note: Different connector configurations that are not listed may be available upon request via [Abracon online support](#)



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

868 / 915 MHz Weather-Proof Whip Antenna



AANE-WH-0039

Request Samples



Check Inventory




Ø13 x 195 mm

RoHS/RoHS II Compliant

MSL Level = N/A

Product Dimensions



Unit : mm

	Name	Material	Finish	QTY
1	Antenna Housing	ABS	Black	1
2	Hinge	ABS	Black	1
3	Housing	ABS	Black	1
4	RF Connector	Copper	Black	1

868 / 915 MHz Weather-Proof Whip Antenna



AANE-WH-0039

Request Samples



Check Inventory




Ø13 x 195 mm

RoHS/RoHS II Compliant

MSL Level = N/A

Measurement Setup (Free Space)



868 / 915 MHz Weather-Proof Whip Antenna



AANE-WH-0039

Request Samples



Check Inventory





Ø13 x 195 mm

RoHS/RoHS II Compliant

MSL Level = N/A

Reflection Characteristics – Return Loss & VSWR



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

868 / 915 MHz Weather-Proof Whip Antenna



AANE-WH-0039

Request Samples



Check Inventory





Ø13 x 195 mm

RoHS/RoHS II Compliant

MSL Level = N/A

Radiation Characteristics – Peak Gain & Average Gain



868 / 915 MHz Weather-Proof Whip Antenna



AANE-WH-0039

Request Samples



Check Inventory




Ø13 x 195 mm

RoHS/RoHS II Compliant

MSL Level = N/A

Radiation Characteristics – Total Efficiency (%)



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

868 / 915 MHz Weather-Proof Whip Antenna



AANE-WH-0039

Request Samples



Check Inventory







Ø13 x 195 mm

RoHS/RoHS II Compliant

MSL Level = N/A

Radiation Characteristics – 3D & 2D Pattern (Free Space)

868MHz



868 / 915 MHz Weather-Proof Whip Antenna



AANE-WH-0039

Request Samples



Check Inventory




Ø13 x 195 mm


RoHS/RoHS II Compliant

MSL Level = N/A


915MHz




XY plane



XZ plane



YZ plane



868 / 915 MHz Weather-Proof Whip Antenna



AANE-WH-0039

Request Samples



Check Inventory



Ø13 x 195 mm

RoHS/RoHS II Compliant

MSL Level = N/A

Packaging

Number of antennas / PE bag: 40 pcs

Number of PE bags / carton: 10

Total antennas / carton: 400 pcs

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf ('COTS'), which are designed, intended, and validated for use in commercial, industrial, and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08-26-25

ABRACON IS
ISO9001-2015
CERTIFIED