

Undervoltage release, TeSys GV4, MN coil, 220 to 240VAC 50Hz 208 to 240VAC 60Hz

GV4AU247

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	TeSys	
Device short name	MN	
Product or Component Type	Voltage release	
Device Application	Control	
Range compatibility	TeSys TeSys GV4 TeSys TeSys BV4	
Voltage release type	Undervoltage release	
[Uc] control circuit voltage	220240 V AC 50 Hz 208240 V AC 60 Hz	

Complementary

[Ui] rated insulation voltage	240 V IEC 60947-1	
Threshold tripping voltage	< 0.35 Un failsafe opening 0.350.7 Un possible opening 0.851.1 Un enabled closing	
Mounting Mode	Internal mounting	
Maximum inrush power in VA	7 VA	
Maximum hold-in power consumption in VA	7 VA	
Mechanical durability	20000 cycles	
Operating time	< 50 ms	
Connections - terminals	Spring terminals 1 0.00080.002 in² (0.51.5 mm²) - cable stiffness: flexible without cable end	
Wire stripping length	0.3 in (8 mm)	

Environment

Quantity per Set Set of 1

Ordering and shipping details

Category	US10I1122366	
Discount Schedule	0111	
GTIN	3606485444840	
Returnability	No	
Country of origin	FR	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type of Package 1	PCE	
Nbr. of units in pkg.	1	
Package 1 Height	1.42 in (3.6 cm)	
Package 1 Width	2.44 in (6.2 cm)	
Package 1 Length	3.39 in (8.6 cm)	
Package weight(Lbs)	2.3 oz (64.0 g)	
Unit Type of Package 2	BB1	
Number of Units in Package 2	10	
Package 2 Height	3.46 in (8.8 cm)	
Package 2 Width	5.20 in (13.2 cm)	
Package 2 Length	7.32 in (18.6 cm)	
Package 2 Weight	24.3 oz (690.0 g)	
Unit Type of Package 3	S03	
Number of Units in Package 3	60	
Package 3 Height	11.81 in (30.0 cm)	
Package 3 Width	11.81 in (30.0 cm)	
Package 3 Length	15.75 in (40.0 cm)	
Package 3 Weight	9.7 lb(US) (4.4 kg)	



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint		
Carbon footprint (kg CO2 eq, Total Life cycle)	252	
Environmental Disclosure	Product Environmental Profile	

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	75582d60-9779-4641-a03b-18e996230a58
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Halogen content performance	Product contains halogen above thresholds

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.