

Product data sheet

Specifications

SQUARE D



Plug in relay, Type KF, flange mounted, 1 HP at 277 VAC, 10A resistive at 277 VAC, DPDT, 2 NO, 2 NC, 120 VAC coil

8501KFR12V20

Product availability: Stock - Normally stocked in distribution facility

Main

product range	8501K
product type	Relay
Relay Type	General purpose
mounting type	Flange
contact composition	DPDT
[Uc] control circuit voltage	120 V AC
pilot light	No indicator
manual operator	Without test button

Complementary

horsepower rating	1 hp 277 V AC 0.33 hp 120 V AC
breaking capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 10 A 277 V AC resistive control circuit UL 508 10 A 30 V DC resistive control circuit UL 508
maximum switching voltage	300 V AC 30 V DC
contact material	Silver alloy (AgNi)
operating time	20 ms - pick-up 20 ms - drop-out
shape of pins	Spade

Environment

ambient temperature range - operational	-40...55 °C (-40...131 °F)
product certifications	UL Recognized CSA CE
Height	2.75 in (69.85 mm)
Width	1.4 in (35.6 mm)
Depth	1.4 in (35.6 mm)

Ordering and shipping details

Category	US10CP221145
Discount Schedule	0CP2

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

GTIN	785901342519
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.70 in (4.318 cm)
Package 1 Width	1.70 in (4.318 cm)
Package 1 Length	3.00 in (7.620 cm)
Package weight(Lbs)	3.040 oz (86.182 g)

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	25

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

 Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No