

SENCITY® Rondo MIMO 2x2 Antenna

1399.31.0010

Properties

- Indoor DAS omni-directional antenna for In-Building Coverage 698 MHz up to 3800 MHz
- AMPS, GSM, PCS, CDMA, UMTS, WiFi, WLAN 2.4, LTE
- Antenna ETL tested for Plenum space (UL 2043)
- Design Patent DM/088510



Electrical bands				
	Band 1	Band 2	Band 3	Band 4
Frequency	698 MHz ... 790 MHz	790 MHz ... 960 MHz	1447 MHz ... 1660 MHz	1695 MHz ... 2170 MHz
VSWR	1.5	1.5	1.7	1.5
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
Gain	2 dBi	2 dBi	4 dBi	6 dBi
Isolation between Ports	20 dB	20 dB	20 dB	23 dB
Ambient Temperature	25 °C	25 °C	25 °C	25 °C
Composite Power max	300 W	180 W	180 W	130 W

	Band 5	Band 6	Band 7
Frequency	2170 MHz ... 2700 MHz	3400 MHz ... 3600 MHz	3600 MHz ... 3800 MHz
VSWR	1.5	1.5	1.5
Impedance	50 Ω	50 Ω	50 Ω
Gain	7 dBi	6 dBi	6 dBi
Isolation between Ports	20 dB	23 dB	30 dB
Ambient Temperature	25 °C	25 °C	25 °C
Composite Power max	90 W	50 W	50 W

Electrical remarks	
IMD level	-155 dBc at carrier power 2x 43 dBm
Remarks	Gain specification defined without use of ground plane. Radiator grounded for remote connectivity surveillance

Ports		
	Port 1	Port 2
Connector	4.3-10, jack (female)	4.3-10, jack (female)
Cable type	SUCOFORM_141_CU_CMP	SUCOFORM_141_CU_CMP
Cable length	0.35 m	0.35 m

SENCITY® Rondo MIMO 2x2 Antenna

1399.31.0010

Ports		
	Port 1	Port 2
Polarization	vertical	vertical
DC grounded	Yes	Yes

Connections		
Port number	Port 1	Port 2
Band 1	✓	✓
Band 2	✓	✓
Band 3	✓	✓
Band 4	✓	✓
Band 5	✓	✓
Band 6	✓	✓
Band 7	✓	✓

Mechanical data	
Weight	0.82 kg
Dimensions	87 mm x 238 mm (Height x Diameter)

Interface and material data	
Radome material	PC (Polycarbonate)
Radome colour	White
Back plate/base plate material	PCB_1


Environmental data	
Operation temperature	0 °C ... 55 °C
Storage temperature	-55 °C ... 85 °C
Transport temperature	-55 °C ... 85 °C
Environment (application)	Indoor
Flammability rating	UL 94-V0
Solar radiation	UL 746C, FI

Environmental remarks
Plenum rated pigtail cable (UL2043)

Additional Information
Item number: 85080511

SENCITY® Rondo MIMO 2x2 Antenna
1399.31.0010

Outline drawing



HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3234 / Date of publication: 13.06.2024 / uncontrolled copy