

Configurable receiver, Harmony XB5R, 2 relays, 2 buttons, 6 indicating LEDs, monostable, bistable, stop start, 24...240V AC DC

ZBRRA

Main

Range of product	Harmony	
Product or component type	Programmable receiver	
Device short name	ZBRRA	
Product specific application	Interface to actuators	
Function of module	Bi-stable Monostable Stop/start	
Reset time	2 ms time delay	
Transmission frequency	2405 MHz	
emission class	5M00G7W	
Antenna type	Omnidirectional	

Complementary

Nominal output current	0.3 A at 48 V DC conforming to IEC 60947-5-1	
	3 A at 24 V DC conforming to UL 508	
	1.5 A at 240 V AC conforming to IEC 60947-5-1	
	3 A at 120 V AC conforming to IEC 60947-5-1	
	3 A at 240 V AC conforming to UL 508	
	3 A at 24 V DC conforming to CSA C22.2 No 14	
	3 A at 240 V AC conforming to CSA C22.2 No 14	
Output type	2 relays	
Output contacts	2 C/O	
Input output isolation	Galvanic isolation	
Time delay range	0.5 s (tolerance: - 1515 %)	
Switching capacity in VA	1250 VA	
Maximum switching current	5 mA AC/DC	
Maximum switching voltage	250 V AC/DC	
[Us] rated supply voltage	24240 V AC/DC 50/60 Hz - 1010 %	
Communication port protocol	Zigbee green power at 2.4 GHz conforming to IEEE 802.15.4	
Maximum sensing distance	100 m in free field	
•	25 m transmitter in a plastic box type XAL D and receiver in a metal enclosure	
	40 m transmitter in box type XAL D, receiver in metal enclosure and use relay-	
	antenna	
Response time	< 30 ms after transmitter clicks	
Utilisation category	AC-15 : B300 conforming to IEC 60947-5-1	
	DC-12 conforming to IEC 60947-5-1	

Maximum power consumption in W	4 W AC/DC
Breaking capacity	15 W
Breaking capacity	750 VA
Control circuit frequency	5060 Hz +/- 10 %
Short-circuit protection	0.4 A fuse type fast blow
Operating position	Any position without derating
Electrical connection	1 conductor cable 0.142.5 mm² - AWG 26AWG 14 - solid - without cable end conforming to IEC 60947-1 2 conductors cable 0.141.5 mm² - AWG 26AWG 16 - solid - without cable end conforming to IEC 60947-1 1 conductor cable 0.144 mm² - AWG 26AWG 12 - flexible - with cable end conforming to IEC 60947-1 2 conductors cable 0.141.5 mm² - AWG 26AWG 16 - flexible - with cable end conforming to IEC 60947-1
Tightening torque	0.51 N.m conforming to IEC 60947-1
Housing material	Self-extinguishing plastic
Status LED	LED green for power ON LEDs green for relay ON LEDs green for function mode LED green and yellow for reception signal
Mounting support	35 mm symmetrical DIN rail conforming to IEC 60715 Mounting plate
Rated short-duration power frequency withstand voltage	1.5 kV 50 Hz conforming to IEC 60947-5-1
[Uimp] rated impulse withstand voltage	4 kV
Surge withstand	1 kV differential mode conforming to IEC 61000-4-5 2 kV common mode conforming to IEC 61000-4-5
Max power consumption in W	1 mW
Number of channels	1
Modulation Technique	O-QPSK
Bandwidth	5 MHz
Antenna gain	0 dBi
Width	36 mm
Height	108 mm
Depth	75 mm
Product weight	0.13 kg
Environment	
Standards	CSA C22.2 No 14 UL 508 IEC 60947-5-1 IEC 60947-1
Radio agreement	RSS SRRC ANATEL ARIB T66 FCC ICASA
Product certifications	C-Tick CCC CSA UL GOST

Marking	CE	
Ambient air temperature for storage	-4070 °C	
Relative humidity	90 % at -2055 °C, without condensation conforming to ETSI EN 300 440-1	
Vibration resistance	+/- 7.5 mm (f= 514 Hz) conforming to IEC 60068-2-6 2 gn (f= 8150 Hz) conforming to IEC 60068-2-6	
Shock resistance	10 gn (duration = 16 ms) for 6000 shocks conforming to IEC 60068-2-27	
IP degree of protection	IP20 (casing) conforming to IEC 60529 IP20 (terminals)	
Pollution degree	2 conforming to IEC 60664-1	
Overvoltage category	II conforming to IEC 60664-1	
Insulation resistance	> 500 MOhm at 500 V DC conforming to NF C 20-030	
[Ui] rated insulation voltage	250 V conforming to IEC 60664-1	
Electromagnetic compatibility	Immunity for industrial environments conforming to IEC 61000-6-2 Conducted and radiated emissions class B conforming to CISPR 22 Electrostatic discharge immunity test - test level: 8 kV (in free air (in insulating parts)) conforming to IEC 61000-4-2 Electrostatic discharge immunity test - test level: 6 kV (on contact (on metal parts)) conforming to IEC 61000-4-2 Susceptibility to electromagnetic fields - test level: 10 V/m (802000 MHz) conforming to IEC 61000-4-3 Susceptibility to electromagnetic fields - test level: 3 V/m (802700 MHz, distance = 20 m) conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test - test level: 2 kV (relay wires) conforming to IEC 61000-4-4 Electrical fast transient/burst immunity test - test level: 2 kV (power supply wires) conforming to IEC 61000-4-4 1.2/50 µs shock waves immunity test - test level: 1 kV (differential mode) conforming to IEC 61000-4-5 1.2/50 µs shock waves immunity test - test level: 2 kV (common mode) conforming to IEC 61000-4-5 Conducted RF disturbances - test level: 10 V conforming to IEC 61000-4-6 Immunity to microbreaks and voltage drops - test level: 10 ms conforming to IEC 61000-4-11 Radiated emission conforming to ETSI EN 300 440-1 Conducted emission conforming to ETSI EN 300 489-3 Radiated emission conforming to ETSI EN 300 440-2	
Electrical durability	100000 cycles	
Mechanical durability	1000000 cycles	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.6 cm
Package 1 Width	8 cm
Package 1 Length	9.6 cm
Package 1 Weight	138 g
Unit Type of Package 2	S03
Number of Units in Package 2	64
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	9.479 kg

Contractual warranty

Warranty

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint		
Total lifecycle Carbon footprint	32	

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	25b7f895-3732-43c8-9910-ef6005058640
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Use Again


○ Repack and remanufacture		
End of life manual availability	End of Life Information	
Take-back	No	
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	

ZBRRA

Dimensions Drawings

Programmable Receiver






Product data sheet

ZBRRA


Mounting and Clearance

Receiver Clearance




- (1) Drive(2) Power Supply or PLC

Receiver Mounting



Connections and Schema

Programmable Receiver




- (1) 500 mA
- (2) Output contacts
- (3) Imax = 3 A

ZBRRA

Technical Illustration

Dimensions



Technical Illustration

Wiring diagram




Image of product / Alternate images

Alternative



