


COAXIAL CONNECTOR, N, 50 Ohm, Straight panel cable jack (female), flange mount
25_N-50-2-9/133_N

Properties

- Screwed coupling mechanism for sturdy and reliable connection
- IP rating (interface, mated) IP67
- Interface dimensions according IEC/MIL



Product configuration		
Gender	Standard	
jack	IEC 61169-16_MIL-STD-348A/304_CECC 22210	
Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating
Electrical data		
Impedance	50 Ω	
Interface frequency	11 GHz	
Mechanical data		
Weight	0.0345 kg	
Mating cycles	500	
Cable entry centre contact	crimped	
Cable entry outer contact	crimped	
Environmental data		
Operation temperature	-65 °C ... 165 °C	

COAXIAL CONNECTOR, N, 50 Ohm, Straight panel cable jack (female), flange mount

25_N-50-2-9/133_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22651072	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22651072	25_N-50-2-9/133_NE	Single

Suitable cables	
Cable group	U2 - 2 mm / 50 Ohm
Suitable cables	RG_316_/U
	RG_188_A/U
Additional cables	RG_174_/U

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22543181	76_Z-0-2-1	Crimping dies

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2490 / Date of publication: 11.07.2025 / uncontrolled copy