


COAXIAL CONNECTOR, BNC, 50 Ohm, Right angle panel receptacle, jack (female), flange mount

28_BNC-50-0-2/133_N

Properties

- Useful for frequently coupled and uncoupled connections
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 4 GHz



Product configuration

Interface type	Gender	Standard
BNC	jack	IEC 60169-8_MIL-STD-348A/301_CECC 22120

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data

Impedance	50 Ω
Interface frequency	4 GHz

Mechanical data

Weight	0.0138 kg
Mating cycles	500
Flange type	square flange / 17.5 X 17.5
Tab style	solder end

Environmental data

Operation temperature	-65 °C ... 165°C
-----------------------	------------------

Ordering Information Table

Item number	Item description	Packaging type
22540500	28_BNC-50-0-2/133_NE	Single

**COAXIAL CONNECTOR, BNC, 50 Ohm, Right angle panel receptacle, jack (female),
flange mount**

28_BNC-50-0-2/133_N

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/
EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for
information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2434 / Date of publication: 26.11.2023 / uncontrolled copy