

COAXIAL ADAPTER, TNC, 50 Ohm, Bulkhead, jack / jack (female / female)

29396G-1

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
TNC	jack (female)	IEC 60169-17_MIL-STD-348A/313_CECC 22200
TNC	jack (female)	IEC 60169-17_MIL-STD-348A/313_CECC 22200

Interface and material data		
TNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Stainless Steel	Passivated (Plating)
Insulator	PFA / PTFE	
TNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Stainless Steel	Passivated (Plating)
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	10 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 10 GHz	16.54 dB	1.35

COAXIAL ADAPTER, TNC, 50 Ohm, Bulkhead, jack / jack (female / female)
29396G-1

Environmental data	
Operation temperature	-55 °C ... 125 °C
Ordering Information Table	
Item number	Item description
80317751	29396G-1

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P38060 / Date of publication: 11.09.2024 / uncontrolled copy