

Contactor, TeSys Deca, 3P(3 NO), AC-3/AC-3e, <=400V, 65A, 230V AC 50/60Hz coil, lugs-ring terminals

LC1D65A6P7

Main

Range	TeSys TeSys Deca	
Range of product	TeSys Deca	
Product or component type	Contactor	
Device short name	LC1D	
Contactor application	Motor control Resistive load	
Utilisation category	AC-4 AC-1 AC-3 AC-3e	
Poles description	3P	
[Ue] rated operational voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC	
[le] rated operational current	80 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 65 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 65 A (at <60 °C) at <= 440 V AC AC-3e for power circuit	
[Uc] control circuit voltage	230 V AC 50/60 Hz	

Complementary

Motor power kW	11 kW at 400 V AC 50/60 Hz (AC-4)	
	18.5 kW at 220230 V AC 50/60 Hz (AC-3)	
	30 kW at 380400 V AC 50/60 Hz (AC-3)	
	37 kW at 500 V AC 50/60 Hz (AC-3)	
	37 kW at 660690 V AC 50/60 Hz (AC-3)	
	18.5 kW at 220230 V AC 50/60 Hz (AC-3e)	
	30 kW at 380400 V AC 50/60 Hz (AC-3e)	
	37 kW at 500 V AC 50/60 Hz (AC-3e)	
	37 kW at 660690 V AC 50/60 Hz (AC-3e)	
Motor power hp	40 hp at 460/480 V AC 50/60 Hz for 3 phases motors	
	5 hp at 115 V AC 50/60 Hz for 1 phase motors	
	10 hp at 230/240 V AC 50/60 Hz for 1 phase motors	
	20 hp at 200/208 V AC 50/60 Hz for 3 phases motors	
	20 hp at 230/240 V AC 50/60 Hz for 3 phases motors	
	50 hp at 575/600 V AC 50/60 Hz for 3 phases motors	
Compatibility code	LC1D	
Pole contact composition	3 NO	
Protective cover	With	
[Ith] conventional free air thermal	10 A (at 60 °C) for signalling circuit	
current	80 A (at 60 °C) for power circuit	
Irms rated making capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1	
	250 A DC for signalling circuit conforming to IEC 60947-5-1	
	1000 A at 440 V for power circuit conforming to IEC 60947	

Rated breaking capacity	1000 A at 440 V for power circuit conforming to IEC 60947	
[Icw] rated short-time withstand current	640 A 40 °C - 10 s for power circuit 900 A 40 °C - 1 s for power circuit	
	110 A 40 °C - 10 min for power circuit	
	260 A 40 °C - 1 min for power circuit	
	100 A - 1 s for signalling circuit	
	120 A - 500 ms for signalling circuit	
	140 A - 100 ms for signalling circuit	
Associated fuse rating	10 A gG for signalling circuit conforming to IEC 60947-5-1	
	125 A gG at <= 690 V coordination type 1 for power circuit	
	125 A gG at <= 690 V coordination type 2 for power circuit	
Average impedance	1.5 mOhm - Ith 80 A 50 Hz for power circuit	
Power dissipation per pole	9.6 W AC-1	
	6.3 W AC-3	
	6.3 W AC-3e	
[Ui] rated insulation voltage	Power circuit: 600 V CSA certified	
,,aa.a.a.a. voitago	Power circuit: 600 V UL certified	
	Signalling circuit: 690 V conforming to IEC 60947-1	
	Signalling circuit: 600 V CSA certified	
	Signalling circuit: 600 V UL certified	
	Power circuit: 690 V conforming to IEC 60947-4-1	
Overvoltage category	III	
Pollution degree	3	
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947	
Safety reliability level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1	
	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO	
	13849-1	
Mechanical durability	6 Mcycles	
Electrical durability	1.4 Mcycles 80 A AC-1 at Ue <= 440 V	
Liectrical durability	1.45 Mcycles 65 A AC-3 at Ue <= 440 V	
	1.45 Mcycles 65 A AC-3e at Ue <= 440 V	
Control circuit type	AC at 50/60 Hz	
Coil technology	Without built-in suppressor module	
	···	
Control circuit voltage limits	0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz	
	0.81.1 Uc (-4060 °C):operational AC 50 Hz	
	0.851.1 Uc (-4060 °C):operational AC 60 Hz 11.1 Uc (6070 °C):operational AC 50/60 Hz	
	25 (55 5 - 5).555.58.61.617.10 - 50/50 - 112	
Inrush power in VA	140 VA 60 Hz cos phi 0.75 (at 20 °C)	
	160 VA 50 Hz cos phi 0.75 (at 20 °C)	
Hold-in power consumption in VA	13 VA 60 Hz cos phi 0.3 (at 20 °C)	
	15 VA 50 Hz cos phi 0.3 (at 20 °C)	
Heat dissipation	45 W at 50/60 Hz	
Onerating time	4 10 ms apaning	
Operating time	419 ms opening 1226 ms closing	
Maximum operating rate	3600 cyc/h at 60 °C	
Oneman Alama Alamania	·	
Connections - terminals	Control circuit: lugs-ring terminals - external diameter: 8 mm Power circuit: lugs-ring terminals - external diameter: 16.5 mm	
Tightening torque	Control circuit: 1.7 N.m - on EverLink BTR screw connectors - with screwdriver flat Ø	
riginering torque	6 mm M3.5	
	Control circuit: 1.7 N.m - on EverLink BTR screw connectors - with screwdriver	
	Philips No 2 M3.5	
	Power circuit: 6 N.m - on EverLink BTR screw connectors hexagonal screw head 10	
	mm M6	
	Control circuit: 1.7 N.m - on EverLink BTR screw connectors - with screwdriver pozidriv No 2	
	Power circuit: 2.5 N.m - on EverLink BTR screw connectors - with screwdriver	
	pozidriv No 2	
Auxiliary contact composition	1 NO + 1 NC	
, composition	1.10 - 1.110	

Auxiliary contacts type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1	
Signalling circuit frequency	25400 Hz	
Minimum switching voltage	17 V for signalling circuit	
Minimum switching current	5 mA for signalling circuit	
Insulation resistance	> 10 MOhm for signalling circuit	
Non-overlap time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact	
Mounting support	Rail Plate	

Environment

Standards	EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 CSA C22.2 No 14 UL 60947-4-1 IEC 60335-2-40:Annex JJ UL 60335-2-40:Annex JJ IEC 60335-1:Clause 30.2	
Product certifications	CCC UL CB Scheme CSA CE UKCA Marine EAC	
IP degree of protection	IP20 front face conforming to IEC 60529	
Protective treatment	TH conforming to IEC 60068-2-30	
Climatic withstand	conforming to IACS E10 exposure to damp heat conforming to IEC 60947-1 Annex Q category D exposure to damp heat	
Permissible ambient air temperature around the device	-4060 °C 6070 °C with derating	
Operating altitude	03000 m	
Fire resistance	850 °C conforming to IEC 60695-2-1	
Flame retardance	V1 conforming to UL 94	
Mechanical robustness	Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor closed (15 Gn for 11 ms) Shocks contactor open (10 Gn for 11 ms)	
Height	122 mm	
Width	55 mm	
Depth	120 mm	
Product weight	0.86 kg	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.400 cm
Package 1 Width	13.900 cm

Package 1 Length	15.500 cm
Package 1 Weight	826.000 g

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint	
Total lifecycle Carbon footprint	84
Environmental Disclosure	Product Environmental Profile

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
PVC free	Yes

Use Again

○ Repack and remanufacture	
End of life manual availability	End of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Technical Illustration

Assembly's dimensions

