

COAXIAL ADAPTER, N-precision - SMA, 50 Ohm, jack / jack (female / female)

31_N-SMA-50-51/1--_U

Properties

- Precision interfaces
- Excellent electrical performance
- Premium base materials and platings



Product configuration		
Interface type	Gender	Standard
N-precision	jack (female)	IEC 60169-16_MIL-STD-348A/402_CECC 22210
SMA-precision	jack (female)	IEC 60169-15_MIL-STD-348A/405_CECC 22110

Interface and material data		
N-precision		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Stainless Steel	
Body	Stainless Steel	
Insulator	Air Dielectric - Bead - PPH	
SMA-precision		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Copper Beryllium Alloy	SUCOPRO Plating
Body	Copper Beryllium Alloy	SUCOPRO Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	18 GHz
VSWR	DC - 18 GHz (≤ 1.025 + 0.007 f GHz)

Mechanical data	
Weight	0.0316 kg
Mating cycles	500

COAXIAL ADAPTER, N-precision - SMA, 50 Ohm, jack / jack (female / female)
31_N-SMA-50-51/1--_U

Environmental data		
Operation temperature		-55 °C ... 70 °C
Ordering Information Table		
Item number	Item description	Packaging type
22543928	31_N-SMA-50-51/1--_UE	Single
Additional Information		
Remarks	Operating specification acc. IEEE Std 287: temperature 13 °C to 33 °C	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2388 / Date of publication: 27.05.2024 / uncontrolled copy