

# GVSBPIT50

## Galaxy VS Maintenance Bypass Cabinet with Input Transformer 30-50kW 480V or 600V In, 208V Out



### Overview

Presentation	Maintenance bypass cabinet with transformer. The maintenance bypass isolates the UPS completely during service operations. The input transformer can be configured onsite for either 480V or 600V input and delivers 208V output. Compatible with 208V UPS.
Lead time	Usually Ships within 2 Weeks

### Physical

Color	White
Height	58.46 in (148.5 cm)
Width	23.62 in (60 cm)
Depth	32.91 in (83.6 cm)
Net Weight	1168.45 lb(US) (530 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

### Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Ambient Air Temperature for Storage	-13...131 °F (-25...55 °C)
Storage Relative Humidity	Non-condensing 0...95 %

### Ordering and shipping details

GTIN	731304342908
Package weight(Lbs)	1234.59 lb(US) (560 kg)

### Packing Units

Package 1 Height	65.75 in (167 cm)
Package 1 width	31.50 in (80 cm)
Package 1 Length	38.98 in (99 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes

---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

---