

COAXIAL ADAPTER, SMA, 50 Ohm, plug / jack (male / female)

33_SMA-50-0-52/199_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
SMA	plug (male)	IEC 60169-15_MIL-STD-348A/310_CECC 22110
SMA	jack (female)	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Interface and material data		
SMA		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	
Coupling nut	Stainless Steel	
SMA		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	18 GHz
VSWR	DC - 18 GHz ($\leq 1.05 + 0.008 f \text{ GHz}$)

Mechanical data	
Weight	0.0059 kg
Mating cycles	500

COAXIAL ADAPTER, SMA, 50 Ohm, plug / jack (male / female)
33_SMA-50-0-52/199_N

Environmental data	
Operation temperature	-65 °C ... 125 °C

Ordering Information Table		
Item number	Item description	Packaging type
22649458	33_SMA-50-0-52/199_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2162 / Date of publication: 27.05.2024 / uncontrolled copy