



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	208 V
Other Input Voltage	240 V
Main Output Voltage	120 V 208 V
Other Output Voltage	240 V
Kw Rating	6400 W
Rated power in VA	8000 VA
Nb of power socket outlets	8 NEMA L5-20R 4 NEMA L14-30R
Output connector type	Hard Wire 4-wire (2PH+N+G) 1
Number of rack unit	19U
Battery Type	Lead-Acid battery
Provided equipment	CD with software Documentation CD Installation guide Rack Mounting support rails User Manual Web/SNMP Management Card

General

Product web sub-family	4kVA power increments
Number of power module free slots	3
Number of power module filled slots	2
Redundant	Yes

Physical

Color	Black Silver
Height	32.91 in (83.6 cm)
Width	18.58 in (47.2 cm)
Depth	27.09 in (68.8 cm)
Net Weight	437.93 lb(US) (198.64 kg)
Mounting Location	Front
Mounting preference	Lower

Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	No

Input

Input Frequency	45...65 Hz auto-sensing
Number of input connectors	1 Hard Wire 4-wire (2PH+N+G)
Efficiency at full load	96...138 V line to neutral
Input Total Harmonic Distortion	Less than 7% for full load
Input Power Factor at Full Load	0.98

Output

Max Configurable Power (Watts)	12800 W
Harmonic distortion	Less than 5 % at full load
Output Frequency (sync to mains)	47...63 Hz sync to mains 60 Hz +/- 0.1 % for 60 Hz nominal not synced 50 Hz +/- 0.1 % for 50 Hz nominal not synced
Crest factor	Up to 5 : 1
Topology	Double Conversion Online
Waveform Type	Sine wave
Bypass type	Internal Bypass (Automatic and Manual) Optional External Bypass
Maximum output current	37 A
Maximum configurable power in VA	16000 VA

Conformance

Product Certifications	CSA
Standards	FCC Part 15 class A OSHDP UL 1778

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...15000 ft (0.00...4572.00 m)
Acoustic level	62 dBA
Heat dissipation	4995 Btu/h

Batteries & Runtime

Included Battery Modules	2
Battery Slots Empty	2
Typical recharge time	3 h
Additional information	Configurable for 120/208 or 120/240 output voltage
Battery Charge Power (Watts)	574 W rated
Battery power in VAh	1728 VAh runtime
Battery Life	3...5 year(s)
Battery option	SYBT5 2 3456 VAh SYARMXR3B3 1 4320 VAh SYARMXR3B3 2 6912 VAh SYARMXR9B9 1 9504 VAh SYARMXR9B9 2 17280 VAh SYARMXR9B9 3 25056 VAh SYARMXR9B9 4 32832 VAh SYARMXR9B9 5 40608 VAh
Extendable Run Time	1

Communications & Management

Free slots	1
Pre-Installed SmartSlot™ Cards	Network management card 2 with environmental monitoring
Control panel	Multi-function LCD status and control console
Audible Alarm	Audible and visible alarms prioritized by severity
Emergency Power Off (EPO)	Yes

Ordering and shipping details

Package weight(Lbs)	528.14 lb(US) (239.56 kg)
---------------------	---------------------------

Packing Units

Package 1 Height	41.50 in (105.4 cm)
Package 1 width	23.58 in (59.9 cm)
Package 1 Length	39.25 in (99.7 cm)
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------