


# COAXIAL SURGE PROTECTOR DEVICE, High-power/low-IM GDT hybrid technology

3409.41.0044-EX

## Properties

- DC continuity for remote powering
- RF peak power not limited by gas discharge tube
- Excellent low PIM performance; Ideal for multicarrier systems
- Availability for application bands between 380 MHz and 18 GHz
- Gas discharge tube installed with SEMPER configuration



## Product configuration

Main path connectors	Port 1: unprotected, 7/16 plug (male) Port 2: protected, 7/16 jack (female)
Mounting and grounding	M8 (screw), brk (bracket)
EMP can be install reversed	YES

## Interface and material data

Housing material / plating	Brass / SUCOPLATE (R) Plating
Center contact, material / plating	Port 1: Brass / Silver Plating Port 2: Copper Beryllium Alloy / Silver Plating

## Electrical data

Impedance	50 $\Omega$
Frequency frame	806 MHz to 2500 MHz
Return loss typical	20.8 dB
Insertion loss typical	0.15 dB
CW power frame	1500 W
Peak power frame	20000 W
PIM 3rd order	-150 dBc typ.
AISG frequency	2176 MHz
AISG return loss	20 dBc typ.
AISG insertion loss	0.1 dBc typ.
DC current	$\leq 2.5$ A at 48 V $\leq 4$ A at 27 V $\leq 6$ A at 24 V $\leq 13$ A at 17 V
Turn-off time	20 sec. typically at 2.0 A and 25°C ambient temperature

**COAXIAL SURGE PROTECTOR DEVICE, High-power/low-IM GDT hybrid technology**

3409.41.0044-EX

Electrical data	
	< 40 sec. typically below 1 A and 25°C ambient temperature
Recovery time	7 sec. at 25°C ambient temperature
Residual pulse energy (typ.)	250 µJ (test pulse 4 kV 1.2/50 µs; 2 kA 8/20 µs)
Surge current handling capability	30 kA single, 20 kA multiple (test pulse 8/20 µs)

Electrical bands		
	Range 1	Range 2
Frequency range	806 MHz ... 960 MHz	1710 MHz ... 2500 MHz
Return loss typical	26 dB	26 dB
Insertion loss	0.15 dB	0.15 dB
Power avg. / peak	3000 W / 20000 W	1500 W / 20000 W
PIM 3rd order	-150 dBc typ.	-150 dBc typ.

Electrical remarks	
DC supply voltage	48 V
DC current	2.5 A
Gas tube	Yes DC, GDT included, replaceable, 9071.99.0748 (SEMPER, 90 V)

Mechanical data	
Weight	407 g
Mating cycles	500

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	IP66
Thermal shock according	MIL-STD-202, Method 107, Cond. B
Vibration according	MIL-STD-202, Method 204, Cond. A
Moisture resistance according	MIL-STD-202, Method 106

Ordering Information Table	
Item number	Item description
23029351	3409.41.0044-EX

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.  
DOCUMENT PIM-PI945 / Date of publication: 31.10.2024 / uncontrolled copy