

COAXIAL ADAPTER, BNC - N, 50 Ohm, Bulkhead, jack / jack (female / female)

34_BNC-N-50-1/133_U

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
BNC	jack (female)	IEC 61169-8_MIL-STD-348A/301_CECC 22120
N	jack (female)	IEC 61169-16_MIL-STD-348A/304_CECC 22210

Interface and material data		
BNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer		SUCOPLATE (R) Plating
N		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body		SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	
Fastening nut	Brass	
Washer	Bronze	

Electrical data	
Impedance	50 Ω
Interface frequency	4 GHz

COAXIAL ADAPTER, BNC - N, 50 Ohm, Bulkhead, jack / jack (female / female)
34_BNC-N-50-1/133_U

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 4 GHz	20 dB	1.22
Mechanical data		
Weight	0.0405 kg	
Mating cycles	500	
Environmental data		
Operation temperature	-65 °C ... 165 °C	
Ordering Information Table		
Item number	Item description	Packaging type
22651055	34_BNC-N-50-1/133_UE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2119 / Date of publication: 12.04.2024 / uncontrolled copy