


RESISTIVE POWER DIVIDER, 50 Ohm, BNC

4901.01.B

Properties

- Very low return loss
- Broadband down to DC
- Effective solution to tap off a signal



Interface and material data	
Interface side 1	BNC / jack (female)
Standard side 1	IEC 60169-8_MIL-STD-348A/301_CEECC 22120
Center contact, material / plating	Brass / Gold Plating (without Nickel underplating)
Outer contact, material / plating	Brass / SUCOPLATE (R) Plating
Body, material / plating	Brass / SUCOPLATE (R) Plating
Insulator, material	PFA / PTFE
Coupling nut, material / plating	Brass / SUCOPLATE (R) Plating
Interface side 2	BNC / jack (female)
Standard side 2	IEC 60169-8_MIL-STD-348A/301_CEECC 22120
Center contact, material / plating	Copper Beryllium Alloy / Gold Plating (without Nickel underplating)
Outer contact, material / plating	Brass / SUCOPLATE (R) Plating
Body, material / plating	Brass / SUCOPLATE (R) Plating
Insulator, material	PFA / PTFE
Interface side 3	BNC / jack (female)
Standard side 3	IEC 60169-8_MIL-STD-348A/301_CEECC 22120
Center contact, material / plating	Copper Beryllium Alloy / Gold Plating (without Nickel underplating)
Outer contact, material / plating	Brass / SUCOPLATE (R) Plating
Body, material / plating	Brass / SUCOPLATE (R) Plating
Insulator, material	PFA / PTFE
Electrical data	
Impedance	50 Ω
Electrical remarks	
Power rating	W at °C ambient temperature. Linearly derated to W at °C ambient temperature.

RESISTIVE POWER DIVIDER, 50 Ohm, BNC
4901.01.B

Mechanical data	
Weight	0.0776 kg

Compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22550078	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table	
Item number	Item description
22550078	4901.01.B

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1893 / Date of publication: 28.02.2025 / uncontrolled copy