


COAXIAL FIXED ATTENUATOR, 50 Ohm, 20 dB, SMA

6820.19.A

Properties

- Wide range of interfaces
- Various bandwidth to improve the impedance matching between subsystems of its waveform
- Used in many test and measurement and communication applications.

**Product configuration**

Interface	Gender	Standard
SMA	plug (male)	IEC 60169-15_MIL-STD-348A/310_CECC 22110
SMA	jack (female)	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Electrical data

Impedance	50Ω
Operating frequency	0 GHz ... 18 GHz
Attenuation nominal	20 dB
VSWR	1.35
Return loss	16.5 dB

Electrical Data (frequency related)

Frequency range	Attenuation deviation	VSWR max
0 GHz to 4 GHz	+/- 0.5 dB	1.1
4 GHz to 8 GHz	+/- 0.6 dB	1.2
8 GHz to 12.4 GHz	+/- 0.8 dB	1.2
12.4 GHz to 18 GHz	+/- 1 dB	1.35

Electrical Data (power)

Average power	1 W at 30 °C ambient temperature. Linearly derated to 0 W at 130 °C ambient temperature.
Peak power	500 W, 5 μs pulse width, 0.05 % duty cycle
Electrical remarks	Peak voltage max. 160V (50 Ohm)

Interface and material data

Interface	SMA / plug (male)	
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating

COAXIAL FIXED ATTENUATOR, 50 Ohm, 20 dB, SMA
6820.19.A

Interface and material data		
Outer conductor	Copper Beryllium Alloy	Gold Plating
Body	Copper Beryllium Alloy	Gold Plating
Insulator	PFA / PTFE	
Coupling nut	Bronze	Gold Plating
Gasket	VMQ (Silicone rubber)	
Interface	SMA / jack (female)	
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer conductor	Copper Beryllium Alloy	Gold Plating
Body	Copper Beryllium Alloy	Gold Plating
Insulator	PFA / PTFE	

Mechanical data	
Weight	0.008 kg

Environmental data	
Operation temperature	-55 °C ... 130 °C

Ordering Information Table	
Item number	Item description
22550042	6820.19.A

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver:
Facts and figures herein are for information only and do not represent any warranty of any kind.