

Product data sheet

Specifications



module XPS-CM - single-beam photo-electric sensors - 24 V DC

XPSCM1144

⚠ To be discontinued on: Dec 30, 2025

⚠ To be end-of-service on: Dec 30, 2026

⚠ To be discontinued

Main

Range of product	Telemecanique Safety light curtains XUSL
Product or component type	Safety module
Safety module name	XPSCM
Safety module application	For monitoring of single beam photo-electric sensor
Function of module	Built-in muting
Safety level	Can reach category 2 with the appropriate control system and correctly wired conforming to EN/ISO 13849-1 Can reach SIL CL 1 with the appropriate control system and correctly wired conforming to EN/IEC 62061 Can reach PL = c with the appropriate control system and correctly wired conforming to EN/ISO 13849-1
Safety reliability data	MTTFd = 16.6 years conforming to EN/ISO 13849-1 DC = 95.5 % conforming to EN/ISO 13849-1 PFH = 3.12E-7 1/h conforming to EN/IEC 61508 PFHd = 3.12E-7 1/h conforming to EN/IEC 62061
Number of inputs	2 (terminal(s) MA, MB) for muting function 4 (terminal(s) Z1, Z2, Z3, Z4) for sensor
Input voltage	24 V DC for sensor 24 V DC (terminal(s) U+, U-) for muting function
Input compatibility	XC limit switch for muting function XU2M18PP340... for muting function XU2S18PP340... (infrared) for sensor XU9M18PP340... for muting function
Connections - terminals	Captive screw clamp terminals, 1 x 0.14...1 x 2.5 mm ² solid or flexible without cable end Captive screw clamp terminals, 1 x 0.25...1 x 1.5 mm ² flexible with cable end, with bezel Captive screw clamp terminals, 1 x 0.25...1 x 2.5 mm ² flexible with cable end, without bezel Captive screw clamp terminals, 2 x 0.14...2 x 0.75 mm ² solid or flexible without cable end Captive screw clamp terminals, 2 x 0.25...2 x 1 mm ² flexible with cable end, without bezel Captive screw clamp terminals, 2 x 0.5...2 x 1.5 mm ² flexible with cable end, with double bezel
Output type	Relay 2 NO (13-14, 23-24), volt-free
Number of additional circuits	0
[Us] rated supply voltage	24 V DC - 20...20 %

Complementary

Sensor power supply	U+, U-: 24 V DC
Maximum supply current for sensors	200 mA

Input current	200 mA for muting function
Synchronisation time between inputs	3 s (+/- 20 %) for the activation of the MA/MB muting signal
Muting maximum duration	60 s (- 10...30 %)
Maximum line resistance	10 Ohm for sensor power supply
Breaking capacity	180 VA holding AC-15 C300 relay output 1800 VA inrush AC-15 C300 relay output
Breaking capacity	20 mA at 24 V for solid state output 1.5 A at 24 V (DC-13) time constant: 50 ms for relay output
Associated fuse rating	4 A gG for relay output conforming to DIN VDE 0660 part 200 4 A gG for relay output conforming to EN/IEC 60947-5-1 6 A fast blow for relay output conforming to DIN VDE 0660 part 200 6 A fast blow for relay output conforming to EN/IEC 60947-5-1
Minimum output current	10 mA for relay output
Minimum output voltage	17 V for relay output
Maximum response time on input open	25 ms
Local signalling	1 LED, function electronic internal fuse status 1 LED, function restarting 1 LED, function safety outputs closed 1 LED, function safety outputs open 1 incandescent lamp, function muting power consumption: 4...6.5 W
Output thermal current	5.6 A per relay 11 A maximum
Power consumption in W	15 W
Protection type	Electronic internal fuse
[Ui] rated insulation voltage	300 V (pollution degree 2) conforming to DIN VDE 0110 parts 1 and 2 300 V (pollution degree 2) conforming to EN/IEC 60947-5-1
[Uiimp] rated impulse withstand voltage	4 kV overvoltage category III conforming to DIN VDE 0110 parts 1 and 2 4 kV overvoltage category III conforming to EN/IEC 60947-5-1

Environment

Ambient air temperature for operation	-10...55 °C
Ambient air temperature for storage	-25...85 °C
IP degree of protection	IP20 (terminals) conforming to IEC 60529 IP40 (enclosure) conforming to IEC 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.4 cm
Package 1 Width	11.6 cm
Package 1 Length	16.0 cm
Package 1 Weight	400.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	20
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm

Package 2 Weight 8.564 kg

Contractual warranty

Warranty 18 months



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint	650
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	72074428-0ffd-4bdf-ae6e-88e966f0bef1
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
PVC free	Yes

Use Again

Repack and remanufacture

End of life manual availability	End of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Dimensions Drawings

Dimensions

