


COAXIAL FIXED ATTENUATOR, 50 Ohm, 30 dB, TNC

6830.26.A

Properties

- Wide range of interfaces
- Various bandwidth to improve the impedance matching between subsystems of its waveform
- Used in many test and measurement and communication applications.

**Product configuration**

Interface	Gender	Standard
TNC	plug (male)	IEC 60169-17_MIL-STD-348A/313_CECC 22200
TNC	jack (female)	IEC 60169-17_MIL-STD-348A/313_CECC 22200

Electrical data

Impedance	50Ω
Operating frequency	0 GHz ... 12.4 GHz
Attenuation nominal	30 dB
VSWR	1.4
Return loss	15.6 dB

Electrical Data (frequency related)

Frequency range	Attenuation deviation	VSWR max
0 GHz to 4 GHz	+/- 1 dB	1.12
4 GHz to 8 GHz	+/- 1 dB	1.2
8 GHz to 11 GHz	+/- 1.5 dB	1.3
11 GHz to 12.4 GHz	+/- 1.5 dB	1.4

Electrical Data (power)

Average power	1 W at 30 °C ambient temperature. Linearly derated to 0 W at 130 °C ambient temperature.
Peak power	500 W, 5 μs pulse width, 0.05 % duty cycle
Electrical remarks	Peak voltage max. 160V (50 Ohm)

COAXIAL FIXED ATTENUATOR, 50 Ohm, 30 dB, TNC
6830.26.A

Interface and material data		
Interface	TNC / plug (male)	
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Interface	TNC / jack (female)	
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Mechanical data	
Weight	0.029 kg

Environmental data	
Operation temperature	-55 °C ... 130 °C

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver:
Facts and figures herein are for information only and do not represent any warranty of any kind.