

Gas discharge tube 1500 V

9071.99.0054

Properties

- Designed for operations exceeding 25 years
- GDT specification according to international standard ITU-T K.12
- Two electrode gas discharge tube 8x8 mm with holder



Interface and material data

Housing material / plating	Brass / SUCOPLATE (R) Plating
----------------------------	-------------------------------

Electrical data

CW power frame	≤ 5980 W
DC sparkover	1500 V, +/- 15 % (@ 100 V/s)
Impulse sparkover 1000 V/μs	3500 V
Insulation resistance	> 10 GΩ (@ 100 V)
Glow voltage	90 V (@ 10 mA)
Arc voltage	approx. 15 V (@ > 1 A)
Capacitance	< 2 pF (@ 1 MHz)
Impulse discharge current	≥ 1 operations (@ 30 kA, 8/20 μs)
	≥ 10 operations (@ 15 kA, 8/20 μs)

Mechanical data

Weight	12 g
--------	------

Environmental data

Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	Unmated / IP66, IP68, according to IEC 60529 (24 h of water, 1 m)

Compliance

Item number	Directive / Regulation	Rating	Exemptions / Details
22544819	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Gas discharge tube 1500 V
9071.99.0054

Additional Information	
Remarks	Test methods per ITU-T (CCITT) K.12, IEEE C62.31, RUS PE-80, Telcordia GR 1361
	Fits to H+S Lightning Protector series 3401, 3402 and 3408.
	Excluding the 3000 series that have the below designations: 3402.xy.30zw For the moment 3000 series only with N and TNC interfaces -> xy=17 or 26
With capsule holder	Yes

Ordering Information Table	
Item number	Item description
22544819	9071.99.0054 (73_Z-0-0-54)

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P44227 / Date of publication: 01.03.2025 / uncontrolled copy