

GNSSoF

Power supply, DC to DC, GNSS over fiber, 2 power IN, 2 power OUT

Direct GPSoF DC/DC Converter

Properties

- 18-75VDC to 12VDC converter designed to power HUBER+SUHNER GPS-over-Fiber and Direct GPS-over-Fiber.
- Allows for stable power infrastructure of up to two GPS-over Fiber products.
- 2 input ports for redundancy support



General data	
Suitable Products	GPSoF16-2 (RX) 85145447 Direct GPSoF - MAC8-1 (RX) 85128283 GPSoF Amp Expansion Module 32 85128404
Product family	GNSSoF auxiliary tools
Electrical data	
Power in	48 VDC
Power connector	3pole connector series 680, socket
Supply voltage range	18 V DC ... 75 V DC
Supply voltage typical	48 V DC
Mechanical data	
Rack height unit	1 U
Environmental data	
Storage temperature	-40 °C ... 85 °C
Operation case temperature	-40 °C ... 55 °C
Humidity receiver in % max	5 - 95 %
Scope of delivery	
2x pieces 2m (3x 0.75mm ²) 3 pole connector assembly	
Ordering Information Table	
Item number	Item description
85152769	Direct GPSoF DC/DC Converter

GNSSoF

Power supply, DC to DC, GNSS over fiber, 2 power IN, 2 power OUT

Direct GPSoF DC/DC Converter

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P44159 / Date of publication: 01.04.2025 / uncontrolled copy