

# MICROBEND R-5, SMA (male), SMA (male), ruggedized, 50 Ohm, 26.5 GHz, 5 in, 127 mm

## MICROBEND R-5

### Properties

- Applicable up to 26.5 GHz
- Part of the "bend-to-the-end" MINIBEND product family
- Direct replacement for 047 size Semi-Rigid cables
- Tightest bend radius in the MINIBEND family
- Solderless cable junction
- Compliant to MIL-DTL-17 (cable) and MIL-PRF-39012 (connectors)



### Product configuration

|                              |                      |
|------------------------------|----------------------|
| Type of cable                | MICROBEND R (3204IE) |
| Type description connector A | 29094CR-32-4I        |
| Series connector A           | SMA, straight - plug |
| Type description connector B | 29094CR-32-4I        |
| Series connector B           | SMA, straight - plug |
| Length                       | 127 mm               |
| Length                       | 5 inch               |
| Length type                  | REF to REF           |

### Electrical data

|                          |             |
|--------------------------|-------------|
| Impedance                | 50 $\Omega$ |
| Max. operating frequency | 26.5 GHz    |
| VSWR max                 | 1.45        |
| Propagation velocity     | 70 %        |

### Electrical Data (frequency related)

| Frequency range     | Return loss | VSWR max | Insertion loss |
|---------------------|-------------|----------|----------------|
| 0 GHz ... 2 GHz     | 20.82 dB    | 1.2      | 0.31 dB        |
| 2 GHz ... 18 GHz    | 16.13 dB    | 1.37     | 0.88 dB        |
| 18 GHz ... 26.5 GHz | 14.71 dB    | 1.45     | 1.1 dB         |

MICROBEND R-5, SMA (male), SMA (male), ruggedized, 50 Ohm, 26.5 GHz, 5 in, 127 mm  
MICROBEND R-5

| Mechanical data        |                   |
|------------------------|-------------------|
| Cable diameter         | 1.91 mm           |
| Static bending radius  | 1.52 mm           |
| Dynamic bending radius | 4.57 mm           |
| Environmental data     |                   |
| Operation temperature  | -55 °C ... 125 °C |
| Ordering information   |                   |
| Item number            | Item description  |
| 80336662               | MICROBEND R-5     |

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.  
DOCUMENT PIM-P38071 / Date of publication: 04.12.2024 / uncontrolled copy