

discrete output module, Modicon TM3, 16 outputs transistor PNP, spring

TM3DQ16TG

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Modicon TM3 Discrete output module	
Product or Component Type		
Range Compatibility	Modicon M241	
	Modicon M251	
	Modicon M221	
	Modicon M262	
Discrete output logic	Positive logic (source)	

Complementary

Maximum cable distance between devices	Unshielded cable <98.4 ft (30 m) transistor output	
Local signalling	1 LED per channel (green) for output status	
Mounting support	Top hat type TH35-15 rail IEC 60715 Top hat type TH35-7.5 rail IEC 60715 plate or panel with fixing kit	
Height	3.5 in (90 mm)	
Width	1.08 in (27.4 mm)	
Depth	3.3 in (84.6 mm)	
Net Weight	0.24 lb(US) (0.11 kg)	

Environment

Marking	CE
Pollution degree	2

Ordering and shipping details

Category	US10MSX22533
Discount Schedule	0MSX
GTIN	3606480611490
Returnability	Yes
Country of origin	TW

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	2.95 in (7.5 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	4.92 in (12.5 cm)
Package 1 Length	4.13 in (10.5 cm)
Package weight(Lbs)	8.6 oz (245.0 g)
Unit Type of Package 2	S04
Number of Units in Package 2	42
Package 2 Height	11.81 in (30 cm)
Package 2 Width	15.75 in (40 cm)
Package 2 Length	23.62 in (60 cm)
Package 2 Weight	24.853 lb(US) (11.273 kg)
Unit Type of Package 3	P12
Number of Units in Package 3	504
Package 3 Height	41.34 in (105 cm)
Package 3 Width	47.24 in (120 cm)
Package 3 Length	31.50 in (80 cm)
Package 3 Weight	273.4 lb(US) (124 kg)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	34
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	7cc01735-94b8-432b-9a81-f9da4dd7709d
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
PVC free	Yes


Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

TM3DQ16TG

Dimensions Drawings

Dimensions




(*) 8.5 mm/0.33 in. when the clamp is pulled out.


Product data sheet

TM3DQ16TG


Mounting and Clearance

Spacing Requirements







Mounting on a Rail



Incorrect Mounting




Mounting on a Panel Surface



(1) Install a mounting strip

Mounting Hole Layout




TM3DQ16TG

Connections and Schema

Digital Transistor Output Module (16-Channel, Source)

Wiring Diagram



(*) Type T fuse