

COAXIAL CONNECTOR, MMBX, 50 Ohm, Straight cable plug (male)

11_MMBX-50-2-2/111_N

Properties

- Smallest board-to-board distance
- Very high frequencies
- Excellent return loss values
- Blind mateable
- Reliable and secure connection

**Product configuration**

Interface type	Gender	Standard
MMBX	plug	HUBER+SUHNER-MMBX

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer conductor	Copper Beryllium Alloy	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

Electrical data

Impedance	50 Ω
Interface frequency	12.4 GHz

Mechanical data

Weight	0.0007 kg
Mating cycles	100
Cable entry centre contact	crimped
Cable entry outer contact	crimped

Engagement / Disengagement force

	Engagement	Disengagement
Interface force min		8 N
Interface force max	30 N	30 N

COAXIAL CONNECTOR, MMBX, 50 Ohm, Straight cable plug (male)

11_MMBX-50-2-2/111_N

Environmental data	
Operation temperature	-55 °C ... 155 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
23001744	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
23001744	11_MMBX-50-2-2/111_NE	Single

Suitable cables	
Cable group	U4 - 2 mm / 50 Ohm
Suitable cables	K_02252_D
	G_02232_D
	ENVIROFLEX_316_D

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22543181	76_Z-0-2-1	Crimping dies

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3620 / Date of publication: 12.07.2025 / uncontrolled copy