

COAXIAL CONNECTOR, N, 50 Ohm, Straight cable plug (male)

11_N-50-12-50/033_-

Properties

- Field mountable connector series Quick-fit
- Screwed coupling mechanism for sturdy and reliable connection
- IP rating (interface, mated) IP67
- Interface dimensions according IEC/MIL

**Product configuration**

Interface type	Gender	Standard
N	plug	IEC 61169-4_CECC 22190_DIN 47223_VG 95250

Interface and material data

Piece parts	Material	Plating
Centre contact	Bronze	Silver Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	NR (Natural Rubber)	

Electrical data

Impedance	50 Ω
Interface frequency	7.5 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 2.7 GHz	30 dB	1.065
2.7 GHz ... 3.7 GHz	28 dB	1.08

Mechanical data

Weight	0.091 kg
Mating cycles	500
Cable entry centre contact	plugged
Cable entry outer contact	clamped

COAXIAL CONNECTOR, N, 50 Ohm, Straight cable plug (male)

11_N-50-12-50/033_-

Environmental data	
Operation temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	Mated / IP68 (24 h of water, 1 m)

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84201169	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
84201169	11_N-50-12-50/033_-E	Single

Suitable cables	
Cable group	M12 - 12 mm / 50 Ohm
Suitable cables	SUCOFEEED_1/2_LW
	SUCOFEEED_1/2_FR
	SUCOFEEED_1/2

Additional Information	
Remarks	Suitable for cables with copper and aluminium outer conductor Stripping tool: 85091563 74_Z-0-12-25 Flaring tool: 85006446 74_Z-0-12-8
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
85006446	74_Z-0-12-8	Flaring tool
85091563	74_Z-0-12-25	Cable stripping tool

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3609 / Date of publication: 12.07.2025 / uncontrolled copy