


COAXIAL CONNECTOR, N, 50 Ohm, Straight cable plug (male)

11_N-50-12-61/033_-

Properties

- Field mountable connector series Quick-fit plus
- Screwed coupling mechanism for sturdy and reliable connection
- IP rating (interface, mated) IP67
- Interface dimensions according IEC/MIL

**Product configuration**

Interface type	Gender	Standard
N	plug	IEC 61169-4_CECC 22190_DIN 47223_VG 95250

Interface and material data

Piece parts	Material	Plating
Centre contact	Bronze	Silver Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Other body part	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Electrical data

Impedance	50 Ω
Interface frequency	11 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 2.7 GHz	32 dB	1.052
2.7 GHz ... 3.7 GHz	30 dB	1.065

Mechanical data

Mating cycles	500
Cable entry centre contact	plugged
Cable entry outer contact	clamped

COAXIAL CONNECTOR, N, 50 Ohm, Straight cable plug (male)

11_N-50-12-61/033_-

Environmental data	
Operation temperature	-55 °C ... 85 °C
Ingress protection (IP Rating)	Mated / IP68 (24 h of water, 1 m)

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
85074818	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c

Ordering Information Table		
Item number	Item description	Packaging type
85074818	11_N-50-12-61/033_-E	Single

Suitable cables	
Cable group	U99 - Customer specific
Additional cables	ANDREW/COMMScope HL4RPV-50

Additional Information	
Remarks	Assembly instructions: Foam-DOC-0000799919, Plenum-DOC-0000736630 / Note: Use blade unit 74_Z-0-12-20, 85069095 (colour yellow)
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
85066880	74_Z-0-12-18	Preparing tool
85068959	74_Z-0-12-21	Cable stripping tool
85069095	74_Z-0-12-20	Cable stripping tool
85069099	74_Z-0-12-22	Cable stripping tool
85089069	74_Z-0-12-24	Cable stripping tool

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3607 / Date of publication: 12.07.2025 / uncontrolled copy