


COAXIAL CONNECTOR, SMA, 50 Ohm, Straight cable plug (male)

11_SMA-50-1-53/119_N

Properties

- Excellent return loss
- Intermateable with PC3.5 and SK
- Applicable in frequencies up to 18 GHz

**Product configuration**

Interface type	Gender	Standard
SMA	plug	IEC 60169-15_MIL-STD-348A/310_CEECC 22110

Interface and material data

Piece parts	Material	Plating
Centre contact	Bronze	Gold Plating (Nickel underplated)
Outer conductor	Stainless steel	Gold Plating (Nickel underplated)
Body	Stainless steel	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Coupling nut	Stainless steel	Passivated (Plating)
Gasket	VMQ (Silicone rubber)	

Electrical data

Impedance	50 Ω
Interface frequency	18 GHz

Mechanical data

Weight	0.0023 kg
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	soldered

Environmental data

Operation temperature	-65 °C ... 165 °C
-----------------------	-------------------

COAXIAL CONNECTOR, SMA, 50 Ohm, Straight cable plug (male)

11_SMA-50-1-53/119_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
23013327	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
23013327	11_SMA-50-1-53/119_NH	Bulk 100 pcs

Suitable cables	
Cable group	Y2 - 1 mm / 50 Ohm
	Y15 - 1 mm / 50 Ohm
Suitable cables	SUCOFORM_47_CU
	SR_47_TP_M17

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22544553	74_Z-0-0-52	Positioning aids
22643029	74_Z-0-0-157	Cable stripping tool
22543124	74_Z-0-0-14	Locator

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3487 / Date of publication: 12.07.2025 / uncontrolled copy