

Advanced control unit, TeSys Ultra, 3P, 1.25 to 5A, 690VAC, protection & diagnostic, class 10, 24VDC coil

LUCB05BL

### Main

IVIAIII		
Range	TeSys	
Range of product	TeSys Ultra	
Product name	TeSys Ultra	
Device short name	LUCB	
Product or component type	Advanced control unit	
Device application	Motor control	
	Motor protection	
Product specific application	Basic protection and advanced functions, communication	
main function available	Protection against overload and short-circuit	
	Manual reset	
	Earth fault protection	
	Protection against phase failure and phase imbalance	
Product compatibility	Device have LLID42	
Froduct compatibility	Power base LUB12	
	Power base LUB32	
	Power base LUB38	
	Power base LUB120	
	Power base LUB320	
	Power base LUB380	
	Reversing contactor breaker LU2B12BL	
	Reversing contactor breaker LU2B32BL	
	Reversing contactor breaker LU2B38BL	
[Ue] rated operational voltage	690 V AC	
Network frequency	4060 Hz	
Load type	3-phase motor - cooling: self-cooled	
Utilisation category	AC-44	
	AC-41	
	AC-43	
Motor power kW	1.5 kW at 400440 V AC 50/60 Hz	
	2.2 kW at 500 V AC 50/60 Hz	
	3 kW at 690 V AC 50/60 Hz	
rated motor current adjustment range	1.255 A	
Thermal overload class	Class 10 - frequency limit: 4060 Hz - temperature compensation: -2570 °C	
	conforming to IEC 60947-6-2	
	Class 10 - frequency limit: 4060 Hz - temperature compensation: -2570 °C	
	conforming to UL 508	
Tripping threshold	14.2 x lr +/- 20 %	
Phase failure sensitivity	Yes	
[Uc] control circuit voltage	24 V DC	

## Complementary

Control circuit voltage limits	2027 V for DC circuit 24 V in operation 14.5 V for DC circuit 24 V drop-out	
Typical current consumption	130 mA at 24 V DC I maximum while closing with LUB12 220 mA at 24 V DC I maximum while closing with LUB32 220 mA at 24 V DC I maximum while closing with LUB38 60 mA at 24 V DC I rms sealed with LUB12 80 mA at 24 V DC I rms sealed with LUB32 80 mA at 24 V DC I rms sealed with LUB38	
Heat dissipation	2 W for control circuit with LUB12 3 W for control circuit with LUB32 3 W for control circuit with LUB38	
Operating time	35 ms opening with LUB12 for control circuit 35 ms opening with LUB32 for control circuit 35 ms opening with LUB38 for control circuit 70 ms closing with LUB12 for control circuit 70 ms closing with LUB32 for control circuit 70 ms closing with LUB38 for control circuit	
Reset	Manual reset	
Standards	EN 60947-6-2 IEC 60947-6-2 UL 60947-4-1, with phase barrier CSA C22.2 No 60947-4-1, with phase barrier	
Product certifications	CE UL CSA CCC EAC ASEFA ATEX Marine	
[Ui] rated insulation voltage	690 V conforming to IEC 60947-6-2 600 V conforming to UL 60947-4-1 600 V conforming to CSA C22.2 No 60947-4-1	
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-6-2	
Safe separation of circuit	400 V SELV between the control and auxiliary circuits conforming to IEC 60947-1 400 V SELV between the control or auxiliary circuit and the main circuit conforming to IEC 60947-1	
Fixing mode	Plug-in (front face)	
Width	45 mm	
Height	66 mm	
Depth	60 mm	
Compatibility code	LUCB	
Environment		
IP degree of protection	IP20 front panel and wired terminals conforming to IEC 60947-1 IP20 other faces conforming to IEC 60947-1 IP40 front panel outside connection zone conforming to IEC 60947-1	
Protective treatment	TH conforming to IEC 60068	
Ambient air temperature for operation	-2570 °C	
Ambient air temperature for storage	-4085 °C	
Operating altitude	2000 m	
Fire resistance	960 °C parts supporting live components conforming to IEC 60695-2-12 650 °C conforming to IEC 60695-2-12	
Shock resistance	10 gn power poles open conforming to IEC 60068-2-27 15 gn power poles closed conforming to IEC 60068-2-27	

Vibration resistance	2 gn, 5300 Hz, power poles open conforming to IEC 60068-2-6 4 gn, 5300 Hz, power poles closed conforming to IEC 60068-2-6	
Resistance to electrostatic discharge	8 kV level 3 in open air conforming to IEC 61000-4-2 8 kV level 4 on contact conforming to IEC 61000-4-2	
Resistance to radiated fields	10 V/m 3 conforming to IEC 61000-4-3	
Resistance to fast transients	2 kV class 3 serial link conforming to IEC 61000-4-4 4 kV class 4 all circuits except for serial link conforming to IEC 61000-4-4	
Immunity to radioelectric fields	10 V conforming to IEC 61000-4-6	
Immunity to microbreaks	3 ms	
Immunity to voltage dips	70 % / 500 ms conforming to IEC 61000-4-11	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	8.000 cm
Package 1 Length	9.000 cm
Package 1 Weight	113.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	23
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.885 kg

## **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Total lifecycle Carbon footprint	19
Environmental Disclosure	Product Environmental Profile

#### **Use Better**

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	0f22867c-27de-46b9-965c-a40bbb8a3f0a
REACh Regulation	REACh Declaration
Halogen-free status	Halogen free plastic parts product
PVC free	Yes

### **Use Again**

○ Repack and remanufacture	
End of life manual availability	End of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins