

Product data sheet

Characteristics

8965RO10V02

Contactor, 8965RO, hoist, reversing, 3HP at 480VAC, 3 phase, 120VAC coil, quick connect terminals. open style



Main

Product or Component Type	Reversing Hoist Contactor
Maximum Horse Power Rating	1 Hp 115 V AC, 1 phase 1.5 Hp 230 V AC, 1 phase 3 Hp 230 V AC, 3 phase 3 Hp 460 V AC, 3 phase 3 hp 575 V AC, 3 phase

Complementary

Product Certifications	CSA UL Listed
Poles description	3P
[Uc] control circuit voltage	110 V AC 50 Hz 120 V AC 60 Hz
Phase	3 phase
Range of Product	RO

Ordering and shipping details

Category	21406-8965 R - REVERSING HOIST CONTACTORS
Discount Schedule	CP1
GTIN	785901032168
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.70 in (9.398 cm)
Package 1 Width	4.80 in (12.192 cm)
Package 1 Length	6.50 in (16.51 cm)
Package 1 Weight	29.12 oz (825.538 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	13.00 in (33.02 cm)
Package 2 Width	13.00 in (33.02 cm)
Package 2 Length	16.50 in (41.91 cm)
Package 2 Weight	14.40 lb(US) (6.532 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

California proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

EU RoHS Directive

Under investigation

China RoHS Regulation

 [China RoHS Declaration](#)

Contractual warranty

Warranty

18 months