

SENCITY® Omni-S Thimble

1399.17.0224

Properties

- Omnidirectional compact broadband antenna for Wi-Fi and Cellular bands between 1710 MHz till 7125 MHz
- WiFi-4, WiFi-5, WiFi-6, WiFi-6E 4G and 5G frequencies band
- Small & robust outdoor stick antenna IP66 / IP68 / IP69K
- Direct mount on N type interface of wireless access points



Electrical data				
	Band 1	Band 2	Band 3	Band 4
Frequency	1710 MHz ... 2000 MHz	2000 MHz ... 2700 MHz	2700 MHz ... 4200 MHz	4900 MHz ... 5150 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	2	2	2	2
Gain	1.5 dBi	2 dBi	1.5 dBi	2.5 dBi
HPBW horizontal	360 °	360 °	360 °	360 °
Ambient Temperature	25 °C	25 °C	25 °C	25 °C
Composite Power max	200 W	160 W	120 W	120 W

	Band 5	Band 6
Frequency	5150 MHz ... 5925 MHz	5925 MHz ... 7125 MHz
Impedance	50 Ω	50 Ω
VSWR	2	2
Gain	2.5 dBi	3 dBi
HPBW horizontal	360 °	360 °
Ambient Temperature	25 °C	25 °C
Composite Power max	120 W	120 W

Ports	
	Port 1
Connector	N, plug (male)
Polarization	vertical
DC grounded	No

SENCITY® Omni-S Thimble

1399.17.0224

Mechanical data	
Weight	0.05 kg
Dimensions	55 mm x 22 mm (Height x Diameter)
Remarks	Coupling nut torque: nominal 1Nm & maximum 3Nm

Material data	
Radome material	ASA (acrylic ester-styrene-acrylonitrile)
Radome colour	RAL 7043 (dark grey)

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Transport temperature	-40 °C ... 85 °C
Environment (application)	Outdoor
Ingress protection (IP Rating)	IP66, IP68
Flammability rating	UL 94-HB

Environmental remarks	
Ingress protection IP66, IP68 & IP69K (EN 60529)	
Flammability rating EN 45545; DIN 5510-2	
Temperature range (damp heat) EN 60068-2-30, Test Db, Variant 1 (40°C; 6 cycles)	
Temperature shock EN 60068-2-14, Test N, -45°C/85°C, 1h, 5 cycles	
Vibration and shock EN 61373, category 1, class b (for railway carriage)	

Ordering information		
Item description	Item number	Product name
1399.17.0224	85012283	SENCITY® Omni-S Thimble

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3255 / Date of publication: 26.03.2025 / uncontrolled copy