

safety module, Harmony XPSU, Cat4, features XPSUAK with delayed outputs, 24V AC or DC, screw

XPSUAT13A3AP

Main

Range of product	Harmony Safety Automation			
Product or component type	Safety module XPSUAT			
Safety module name				
Safety module application	Monitoring antivalent contacts For emergency stop, guard and light curtain monitoring Monitoring of pressure-sensitive 4-wire protective devices Emergency stop button with 2 NC contacts Guard monitoring with 1 or 2 limit switches Monitoring 2 PNP sensors Magnetic switch monitoring Light curtain monitoring RFID switch Monitoring of electro-sensitive protection equipment (ESPE) Sensing mat/edges Proximity sensor monitoring Monitoring 1 PNP + 1 NPN sensor Can reach PL e/category 4 for normally open relay contact conforming to ISO 13849-1 Can reach SILCL 3 for normally open relay contact conforming to IEC 62061 Can reach PL c/category 1 for normally closed relay contact conforming to ISO 13849-1 Can reach SILCL 1 for normally closed relay contact conforming to IEC 62061 Can reach SILCL 1 for normally closed relay contact conforming to IEC 62061 Can reach SILCL 1 for normally closed relay contact conforming to IEC 62061 Can reach SILC 1 for normally closed relay contact conforming to IEC 62061			
Function of module				
Safety level				
Safety reliability data	MTTFd > 30 years conforming to ISO 13849-1 Dcavg >= 99 % conforming to ISO 13849-1 PFHd = 0.94E-09 conforming to ISO 13849-1 for SS0 PFHd = 0.95E-09 conforming to ISO 13849-1 for SS1 HFT = 1 conforming to IEC 62061 PFHd = 0.94E-09 conforming to IEC 62061 for SS0 PFHd = 0.95E-09 conforming to IEC 62061 for SS1 SFF > 99% conforming to IEC 62061 HFT = 1 conforming to IEC 61508-1 PFHd = 0.94E-09 conforming to IEC 61508-1 for SS0 PFHd = 0.95E-09 conforming to IEC 61508-1 for SS1 SFF > 99% conforming to IEC 61508-1 Type = B conforming to IEC 61508-1			
Electrical circuit type	NC pair PNP pair Antivalent pair OSSD pair			
Connections - terminals	Removable screw terminal block, 0.22.5 mm² solid or flexible Removable screw terminal block, 0.252.5 mm² flexible with ferrule single conductor Removable screw terminal block, 0.21.5 mm² solid or flexible twin conductor Removable screw terminal block, 2 x 0.251 mm² flexible with ferrule without cable end, with bezel Removable screw terminal block, 2 x 0.51.5 mm² flexible with ferrule with cable end, with bezel			
[Us] rated supply voltage	24 V AC - 1510 % 24 V DC - 2020 %			

Complementary

Synchronisation time between	0.5 s	
inputs	2 s	
	4 s	
Type of start	Automatic/manual/monitored	
Power consumption in W	3 W 24 V DC	
Power consumption in VA	6.5 VA 24 V AC 50/60 Hz	
Input protection type	Internal, electronic	
safety outputs	1 NC configurable	
	3 NO configurable 3 NO immediate	
safety inputs	2 monitive potato import 24 V DC 0 mA	
salety iliputs	2 positive safety input 24 V DC 8 mA 1 negative safety input	
maximum wire resistance	500 Ohm	
Time delay range	0900 s off delay	
Input compatibility	Normally closed circuit conforming to ISO 14119	
	XC limit switch conforming to ISO 14119	
	Mechanical contact conforming to ISO 14119	
	Normally closed circuit conforming to ISO 13850	
	Antivalent pair conforming to ISO 14119 OSSD pair conforming to IEC 61496-1-2	
	3-wire proximity sensors PNP	
	o wile proximity concord i th	
[le] rated operational current	5 A AC-1 for normally open relay contact	
	3 A AC-15 for normally open relay contact	
	5 A DC-1 for normally open relay contact	
	3 A DC-13 for normally open relay contact	
	3 A AC-1 for normally closed relay contact	
	1 A AC-15 for normally closed relay contact	
	3 A DC-1 for normally closed relay contact	
	1 A DC-13 for normally closed relay contact	
control outputs	4 on/off configurable pulsed output	
Input/output type	Semiconductor output 24 V DC, 20 mA Z2, not safety-related Pulsed output for diagnostics 24 V DC, 20 mA Z1, not safety-related	
[Ith] conventional free air thermal current	16 A	
Associated fuse rating	10 A gG for NO relay output circuit conforming to IEC 60947-1	
Minimum output current	20 mA for relay output	
Minimum output voltage	24 V for relay output	
Maximum response time on input open	20 ms	
[Ui] rated insulation voltage	250 V (pollution degree 2) conforming to IEC 60947-1	
[Uimp] rated impulse withstand voltage	4 kV overvoltage category II conforming to IEC 60947-1	
Mounting support	35 mm symmetrical DIN rail	
Depth	120 mm	
Height	100 mm	
Width	45 mm	
Product weight	0.350 kg	

Environment

Standards	IEC 60947-5-1 IEC 61508-1 functional safety standard IEC 61508-2 functional safety standard IEC 61508-3 functional safety standard IEC 61508-4 functional safety standard IEC 61508-5 functional safety standard IEC 61508-6 functional safety standard IEC 61508-7 functional safety standard IEC 61508-7 functional safety standard IEC 62061 functional safety standard			
Product certifications	TÜV cULus			
IP degree of protection	IP54 (mounting area) conforming to IEC 60947-1 IP40 (housing) conforming to IEC 60947-1 IP20 (terminals) conforming to IEC 60947-1			
Ambient air temperature for storage	-2585 °C			
Relative humidity	595 % non-condensing			

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.500 cm
Package 1 Width	15.500 cm
Package 1 Length	13.500 cm
Package 1 Weight	440.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	16
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	7.706 kg
Unit Type of Package 3	P06
Number of Units in Package 3	128
Package 3 Height	77.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	72.160 kg



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Total lifecycle Carbon footprint	106
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	152cf799-1df7-4892-81b4-4c890187f1d1
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
PVC free	Yes


Use Again

○ Repack and remanufacture	
End of life manual availability	End of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Dimensions Drawings

Dimensions

Front and Side Views



(A): Product drawing

(B) : Screw clamp terminal

(C): Side view

(1): Removable terminal blocks, top

(2): Removable terminal blocks, bottom

(3): LED indicators

(4): Start function selector

(5): Function selector

(6): Delay factor selector (7): Delay base selector


(8): Connector for optional output extension module (lateral)

(9): Sealable transparent cover


mm in.	7.0–8.0 0.28–0.31		44		₩	- 8D -
	mm²	0,2 2,5	0,252,5	0,21,5	0,251	0,51,5
	AWG	24 12	2412	2416	2418	2016
		()c@p		Nm	0.5 0.6	
Ø 3,5 mm (0.14 in)				lb-in	4,4 5,3	

Mounting and Clearance

Mounting to DIN rail




Screw-mounting



XPSUAT13A3AP

Connections and Schema

Wiring Drawing



(1): A1-A2 (Power supply)

(2): S11-S12-S21-S22-S31-S32 (Single-channel safety input)

(3): Y1-Y2 (Start)

13-23-33-47-57-67-75-14-24-34-48-58-68-76: Output

EXT: Connector for optional extension module

B2: Common ground terminal

Z1 : Pulsed output for diagnostics, not safety-related

Z2 : Solid state output, not safety-related

Image of product / Alternate images

Alternative

