

SENCITY® OMNI-S stick antenna

1399.17.0232

Properties

- Omni-directional multiband antenna for GSM 1800, GSM/PCS 1900, UMTS, LTE 2300, 2500 and 2600, also WLAN IEEE 802.11 b/g Wi-Fi 2400 to 2500 MHz
- Gain of 2 dBi with Vertical polarisation
- For both indoor and outdoor mounting with IP67 rating
- Bracket for pole or wall mounting is included



Electrical data	
	Band 1
Frequency	1710 MHz ... 2690 MHz
Impedance	50 Ω
VSWR	1.8
Gain	2 dBi
HPBW vertical	65 °
HPBW horizontal	360 °
Ambient Temperature	25 °C
Composite Power max	25 W

Electrical remarks	
IMD level	145 dBc at carrier power 2x 30 dBm

Ports	
	Port 1
Connector	N, jack (female)
Polarization	vertical
DC grounded	Yes

SENCITY® OMNI-S stick antenna

1399.17.0232

Mechanical data	
Weight	0.3 kg
Dimensions	120 mm x 22 mm (Height x Diameter)
Remarks	INCLUDED MOUNTING MATERIAL: Bracket 9091.99.0173 and 2 metal-bands for mast-diameter 25mm - 101mm, all piece parts made of stainless steel

Material data	
Radome material	Glass Fibre
Radome colour	RAL 9003 (signal white)

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-55 °C ... 85 °C
Transport temperature	-40 °C ... 85 °C
Environment (application)	Indoor/Outdoor
Ingress protection (IP Rating)	IP67

Environmental remarks	
LOW TEMPERATURE: IEC 60068-2-1; 72h; -55°C HIGH TEMPERATURE: IEC 60068-2-2; 72h; +85°C HUMIDITY: ETSI EN300-2-4 T4, 1E; 144h; 95% SALT SPRAY: EN 60068-2-11 / GB-T 10125; 96h MECHANICAL SHOCK: IEC 60721-3-4, 4M5 VIBRATION: IEC 60721-3-4; 30 min/axis; random; 4M5	

Additional Information	
Mounting accessory included	

Antenna accessories		
Item description	Item number	Product name
9091.99.0173	23035942	L - bracket for omni stick antennas

Antenna accessories remarks	
9091.99.0173 L - bracket for omni stick antennas	

Ordering information		
Item description	Item number	Product name
1399.17.0232	85026688	SENCITY® OMNI-S stick antenna

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3253 / Date of publication: 14.08.2025 / uncontrolled copy