

# SENCITY® Road MULTI Antenna

1399.19.0412

## Properties

- Supports 2G/3G/4G/5G cellular, Wifi 2.4/5 GHz, Wifi 6E
- 7 separate ports for 4x4 cellular MIMO and 3x3 Wifi MIMO.
- Meets ISO16750 automotive standard
- Single hole mounting, easy cabling feed-through
- Fire retardant acc. to ECE-R118



## Electrical data

|                         | Band 1              | Band 2                | Band 3                | Band 4                |
|-------------------------|---------------------|-----------------------|-----------------------|-----------------------|
| Name                    | Cellular 1-4        | Cellular 1-4          | Cellular 1-4          | Cellular 1-4          |
| Frequency               | 617 MHz ... 960 MHz | 1350 MHz ... 2700 MHz | 3300 MHz ... 4200 MHz | 4900 MHz ... 7125 MHz |
| Impedance               | 50 Ω                | 50 Ω                  | 50 Ω                  | 50 Ω                  |
| VSWR                    | 2                   | 2.1                   | 2                     | 2                     |
| Gain                    | 2 dBi               | 4 dBi                 | 4 dBi                 | 5 dBi                 |
| Isolation between Ports | 9 dB                | 18 dB                 | 15 dB                 | 18 dB                 |
| Ambient Temperature     | 25 °C               | 25 °C                 | 25 °C                 | 25 °C                 |
| Composite Power max     | 40 W                | 40 W                  | 40 W                  | 40 W                  |

|                         | Band 5                | Band 6                |
|-------------------------|-----------------------|-----------------------|
| Name                    | WiFi 1-2              | WiFi 1-2              |
| Frequency               | 2400 MHz ... 2500 MHz | 4900 MHz ... 7125 MHz |
| Impedance               | 50 Ω                  | 50 Ω                  |
| VSWR                    | 2                     | 2                     |
| Gain                    | 6 dBi                 | 6 dBi                 |
| Isolation between Ports | 24 dB                 | 24 dB                 |
| Ambient Temperature     | 25 °C                 | 25 °C                 |
| Composite Power max     | 30 W                  | 30 W                  |

**SENCITY® Road MULTI Antenna**

1399.19.0412

| Electrical remarks |                                                                                                                                                                                                                                                                                                                                                                        |
|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Remarks            | Ground plane: Indicated VSWR values are valid for a metallic ground plane of 0.5 x 0.5m or larger and Isolation is provided as typical values. Indicated VSWR values are mostly valid for installations on non-metallic surfaces also (no specific ground plane requirements). Indicated gain values will be achieved on a metallic ground plane of 1 x 1 m or larger. |

| Ports        |                     |                     |
|--------------|---------------------|---------------------|
|              | Port 1 to 4         | Port 5 to 7         |
| Port name    | Cell 1-4 (White)    | WiFi 1-2 (blue)     |
| Connector    | SMA, plug (male)    | SMA, plug (male)    |
| Cable type   | ENVIROFLEX_316_D-AM | ENVIROFLEX_316_D-AM |
| Cable length | 0.3 m               | 0.3 m               |
| Polarization | vertical            | vertical            |
| DC grounded  | Yes                 | Yes                 |

| Connections |                  |                 |
|-------------|------------------|-----------------|
|             | Port 1 to 4      | Port 5 to 7     |
| Port name   | Cell 1-4 (White) | WiFi 1-2 (blue) |
| Band 1      | ✓                |                 |
| Band 2      | ✓                |                 |
| Band 3      | ✓                |                 |
| Band 4      | ✓                |                 |
| Band 5      |                  | ✓               |
| Band 6      |                  | ✓               |

| Mechanical data       |                                    |
|-----------------------|------------------------------------|
| Weight                | 1.1 kg                             |
| Dimensions            | 60 mm x 210 mm (Height x Diameter) |
| Mounting breakthrough | Ø 30 mm                            |

| Material data                  |                      |
|--------------------------------|----------------------|
| Radome material                | PC (Polycarbonate)   |
| Radome colour                  | RAL 7043 (dark grey) |
| Back plate/base plate material | Aluminium            |

| Environmental data             |                     |
|--------------------------------|---------------------|
| Operation temperature          | -40 °C ... 85 °C    |
| Storage temperature            | -40 °C ... 85 °C    |
| Transport temperature          | -40 °C ... 85 °C    |
| Environment (application)      | Outdoor             |
| Ingress protection (IP Rating) | Mated / IP68, IP69k |
| Flammability rating            | ECE-R118            |
| Solar radiation                | DIN 75220           |

**SENCITY® Road MULTI Antenna**

1399.19.0412

**Environmental remarks**

Environmental tests: ISO 16750:2012/2010

Low corrosion designed acc. to MIL-F-14072D

E-Mark

CE-Mark

**Ordering information**

| Item description | Item number | Product name                |
|------------------|-------------|-----------------------------|
| 1399.19.0412     | 85192479    | SENCITY® Road MULTI Antenna |

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/  
EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for  
information only and do not represent any warranty of any kind.  
DOCUMENT PIM-P35228 / Date of publication: 04.06.2025 / uncontrolled copy